



LIVING K4036 N O W

Double pushbutton






Use


Double pushbutton for lighting and other loads.

Range Related Designation Item **Cover Codes** ☐ KW05L double pushbutton 1 P (NO) + 1 P (NO) K4036 not interlocked, not lightable ■ KM05L - 1 module ■ KG05L ☐ KW05 double pushbutton 1 P (NO) + 1 P (NO) interlocked for shutters, not lightable K4037 ■ KM05 - 1 module

Color code: ☐ White ☐ Sand ☐ Black

Overall dimensions (mm)





■ KG05

	Α	В	C	D
K4036	45.2	22.3	35	2
K4037	45.2	22.3	35	2

Connection

Terminal type: screw clamp
Terminal capacity: 2 x 2,5 mm² max
Stripping length: 9 mm

Compatible with flexible or rigid cables

Technical characteristics

- Protection index

(considering a complete installation, including cover plate) Penetration by solid bodies/liquid: IP40

- Mechanical characteristics

Impact test: IK 04

- Material characteristics

Case: PC (Polycarbonate)

Halogen free.

UV resistant.

Self-extinguishing

 850° C / 30 s for insulating parts holding live parts in place 650° C / 30 s for other parts made of insulating materials

- Electrical characteristics

Voltage: 250 V a.c. Current: 10 A

- Climatic characteristics

Storage temperature: -10° C to $+70^{\circ}$ C Use temperature: -5° C to $+35^{\circ}$ C

Cleaning

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

Caution: Always test before using special cleaning products.

Standards and approvals

Compliance with standards IEC/EN 60669-1.

Refer to e.catalogue.

