


IP44 Universal covers



Use

IP44 protection cover (guaranteed when closed). Ideal for installation where an IP44 protection degree is required. It is fully compatible with all ranges, both BTicino and other brands.

It's made using high quality materials that ensure long-term resistance in all weather conditions.

It can be installed on Italian standard 3-module flush mounted box.

Range		
Designation	ltem	
3 Modules	23603	

Technical characteristics

- Protection index

Penetration by solid bodies/liquid: IP44

- Mechanical characteristics Impact test: IK 07

- Material characteristics

Rigid part : PC - Self-extinguishing: 850° C / 30 s


Fexible part: Acrylic block copolymer elastomer - Self-extinguishing: 650° C / 30 s Halogen free.

UV resistant.

- Climatic characteristics

Storage temperature: -10° C to $+70^{\circ}$ C Use temperature: -5° C to $+35^{\circ}$ C

Overall dimensions (mm)



	Α	В	C	D	
26603	115.6	142.2	26	3	_

Cleaning

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene. \\

Caution: Always test before using special cleaning products.

Standards and approvals

Compliance with standards IEC/EN 60670-1 Refer to e.catalogue.

