


**Connector jack 3.5****Use**

The 3.5mm jack connectors can be used to create audio/video connections.

Equipped with 150 mm long cable.


**Connection**

Type connector: jack 3.5

**Range**

Designation	Item
Connector jack 3.5	<input type="checkbox"/> YW4280
- 1 module	<input checked="" type="checkbox"/> YG4280
	<input checked="" type="checkbox"/> YD4280

**Colors:**  White  Stone  Dark

**Overall dimensions (mm)**

A	B	C	D	E
45.1	22.5	21.5	8.6	10.6

**Technical characteristics****- Protection index:**

(considering a complete installation, including cover plate)

- Penetration by solid bodies/liquid: IP20
- Impact test: IK04

**- Material characteristics:**

- Key cover : ABS
- Halogen Free
- UV resistant
- Self-extinguishing: 650°C/30s

**- Climatic characteristics:**

- Storage temperature: -10°C a +70°C
- Use temperature: -5°C a +35°C

**Cleaning**

Clean the surface with a cloth.

Do not use acetone, tar-removing cleaning agents or trichloroethylene.

**Caution: Always test before using special cleaning products.**

**Standards and approvals**

Compliant with product and installation standard.

Refer to e.catalogue.