


Living Now™

Ref . No. : KG4301V20

20A Switch SP 1M 1M IND

Date : 26/11/2021

Rev.1

**1. USE**

General lighting control mechanism .

2.Type

One way switch (square) single pole

No. of modules : 1

Colour : Black

Mounting : Flush and Surface - mounted

3.OVERALL DIMENSIONS

Width : 22.35 mm

Height : 45.2 mm

Depth : 42.2 mm

Weight (g) : 18.5 gm

4.CONNECTION

Terminal : with screws

Capacity : 2.5mm² to 6mm²

Stripping : 10 mm

Screwdriver : 4mm flat-blade up to 5 mm

5.OPERATION

Switch with rocker

6.TECHNICAL CHARACTERISTICS**6.1 Material Characteristics**

Rocker : Polycarbonate

Base : Polycarbonate

Basket : Polypropylene

Contact Terminal : Brass with Silver plating

Pivot Terminal : Brass with Silver plating

Screws : Brass

Cover : Polycarbonate

Plunger : Polycarbonate

Rocker spring : Stainlesssteel

Transmitter : Polypropylene

Contact Tip : Silver

Moving Contact : Brass with Silver plating

6.2 Electricals Characteristics

Voltage : 230V/250V AC

Current : 20A

Self - extinguishing : 850° C / 30 s.

7.CONFORMITY - APPROVALS

As per IS : 3854