



488 40/41	
	100 - 240 V
	50 - 60 Hz
	2 x 2,5 mm ²
	RJ 45
	≤ 200 mA
NF EN 50428	

230 V~ 110 V~	3680 W 1760 W	16 A	3680 W 1760 W	16 A	10 (2 x 36 W) 5 (2 x 36 W)	4,3 A	3680 VA 1760 VA	16 A	3680 VA 1760 VA	16 A	1150 VA 550 VA	5 A



