



	488 42
	100 - 240 V
	50 - 60 Hz
	2 x 2,5 mm ² 0 - 10 V ≤ 1,5 mm ²
	RJ 45
	≤ 200 mA
	NF EN 50428

230 V~	1000 VA	2 x 4,3 A	1000 VA	2 x 4,3 A	1000 W	2 x 4,3 A
110 V~	500 VA		500 VA		500 W	



