



	488 43
—V—	100 - 240 V
	50 - 60 Hz
	2 x 2,5 mm ² 0 - 10V ≤ 1,5 mm ²
	RJ 45
1← + 2← + 3← + 4←	≤ 200 mA
	NF EN50428

 + 45°C - 5°C			
230 V~	4 x 1000 VA	4 x 4,3 A	4 x 1000 W 4 x 500 W
110 V~	4 x 500 VA	4 x 4,3 A	4 x 4,3 A



