







	100 - 240 V~
	50 / 60 Hz
	2 x 2,5 mm ²
	-5°C / +45°C
	 PIR
	300 lux
	15 mn
	Ø 8 m



230 V	Max.	400 W	1,7 A	400 VA	1,7 A	400 VA	1,7 A
	Min.	40 W	0,2 A	40 VA	0,2 A	40 VA	0,2 A
110 V	Max.	200 W	1,7 A	200 VA	1,7 A	200 VA	1,7 A
	Min.	20 W	0,2 A	20 VA	0,2 A	20 VA	0,2 A

