







C	A	D lcw (mm)					
		5 kA	10 kA	15 kA	20 kA	25 kA	30 kA
TB250CA 4 044 30	250A	1600	800	400	320	250	-
TB400CA 4 044 31	400A	1600	800	533	400	320	250
TB630CA 4 044 32	630A	1600	800	533	400	320	250

