
La legrand




Characteristics

1			IPXX	U	9,000
-10°C +70°C	0°C +35°C	5A/115°C	IP 20	220 240 V~ 50 / 60 Hz	8 mm 12,5 mm ²

	R		L	C /L				
240 V~ 50 Hz	P					Dimmable	Dimmable LED	
	-‡-	☼		⊒ ZI⊗		0	⊒ Z⊗	
	5 150 VA		5 150 VA	5 150 VA	5 150 VA	575W <=10x		


Setting the minimum brightness



With the lamp ON, push and hold the Button until the lamp turns OFF, continue holding the button for 5 seconds, the lamp will switch ON again.


--> Release the button --> Turn the coding switch to adjust the brightness, until you reach the desired lighting level --> Hold the Button down for 5 seconds to memorize the minimum brightness --> Then the lamp switches OFF.

Setting / Reseting the CFL Load




When the lamp is OFF, push and hold down the Button and the lamp will turn ON. Continue holding down the button for 5 seconds, and the lamp will turn OFF again --> Release the button --> Turning left cancels the CFL, the lamp will be ON at 50% brightness, turning right sets the CFL, the Lamp will be ON at Max brightness --> Hold down the Button for 5 seconds, the load type will be memorized --> Then the lamp will switch OFF.

Installation




Restoring the factory setting



When the lamp is ON, push the Button, the lamp will turn OFF, continue holding for 5 seconds, then the lamp will turn ON again --> Hold down for 5 seconds --> The lamp will turn OFF, the system has reset to the default value.

• Normal operation (no connection with long distance terminal)




Press the button (on the dimmer), if the load is ON, it will turn OFF. If the load is OFF, it will turn ON.

Change brightness

When the load is ON (on the dimmer), turn left, brightness will decrease; turn right, brightness will increase.

Normal operation (with long distance terminal)




- -- Press the button (on the dimmer), if the load is ON, then it will turn OFF. If the load is OFF, then it will turn ON.
- -- Press the button (on the switch connected to the long distance terminal) and hold it down for 2 seconds.

Change brightness

- -- When the load is ON (on the dimmer), turn left, brightness will decrease to the minimum; turn right, brightness will increase to the maximum.
- -- Press the button (on the switch connected to the long distance terminal) and hold for longer than 2 seconds, the brightness will increase to the maximum or decrease to the minimum.

Load type selection



- -- Knob of slide switch to the right, use for capacitive load or resistive load
- -- Knob of slide switch to the left, use for inductive load or resistive load

Safety instructions


This product should be installed in line with installation rules, preferably by a qualified electrician. Incorrect installation or use can lead to a risk of electric shock or fire.

Before carrying out installation, read the instructions and take the product's specific mounting location into account.

Do not open, dismantle, alter or modify the device except when specifically required to do so by the instructions. All Legrand products must be opened and repaired exclusively by personnel trained and approved by Legrand

Any unauthorised opening or repairs fully cancels all liabilities as well as the rights of replacement and any guarantees. Use only Legrand brand accessories.

8 32X 51/8 33X51/7 311 51



• المواصفات

	الوحدة	مؤشر الحماية X X	<u></u>		1
8 ملم 2.51 ملم	240 220 فولط~ 60/50 هيرنز	مؤشر الحماية 20	5 أمبير/ 115 °م	0 ° د/م+ 35 ° م	- 10 ° د/م + 70 م

		C/L		L	R		
مصباح اشعاع یودي تدرجي	تدرجي ••••••••••••••••••••••••••••••••••••						240 فولط ~ 50 هيرنز
ZØ	Ü	=	⊒ Z]⊗	0	-\$-	₿	30 میردر
55 فولط = 755 واط أميير => 10X		5150 فولط أمبير	5150 فولط أمبير	5 55 فولط أمبير			


ضبط الإنارة على أدنى مستوى



عندما يكون المصباح مشتعلا، اضغط باستمرار على "الزر" لينطفى. واصل الضغط لمدة 5 ثواني، ليشتعل المصباح من جديد.


--> أترك الزر --> أدر مُفتَّاح الترميز الذي يضبط مستوى الإنارة، حتى تحصل على قيمة ملائمة--> اضغط على "الزر" لمدة 5 ثواني ليسجل الجهاز الحد الأدنى للإنارة في ذاكرته --> و من تم ينطفئ المصباح.

• تشغیل / توقیف تحمیل CFL (مصباح الفلوریسنت المدمج)




عندما يكون المصباح منطفنا، اضغط باستمرار على "الزر" ليشتعل، واصل الضغط لمدة 5 ثواني، لينطفئ المصباح من جديد --> انرك الزر --> أدر الزر نحو اليسار و الغي (مصباح الفلوريسنت المدمج) CFL ، ليشتعل المصباح في حدود 50 % كمستوى للإنارة ، أدر زر جهاز CFL (مصباح الفلوريسنت المدمج) نحو اليمين، ليشتعل المصباح بأقصى مستوى للإنارة --> اضغط على "الزر" لمدة 5 ثواني ليسجل الجهاز التحميل النوعي في ذاكرته --> و من تم ينطفئ المصباح.

• التركيب




الرجوع إلى الضبط الأصلى



عندما يكون المصباح مشتعلا، اضغط على "الزر" لينطفئ، واصل الضغط على الزر لمدة 5 ثواني ليشتعل المصباح من جديد --> واصل الضغط لمدة 5 ثواني --> لينطفئ المصباح. النظام يحمل القيمة الافتراضية.

• اشتغال عادي (عدم التوصيل بمحطة بعيدة المدى)




تشغيل / توقيف ON/OFF

اضغط على زر (جهاز التباين الضوني)، إذا كان التحميل مشتغلا، أدر الزر على وضعية التوقيف، إذا كان التحميل غير مشتغل، و من تم أدر الزر على وضعية التشغيل.

تغيير مستوى الإنارة

عندما يكون التحميل مشتقلا على (جهاز التباين الضوئي)، أدر الزر نحو اليسار لينخفض مستوى الإنارة و أدر الزر نحو اليمين ليرتفع مستوى الإنارة.

• اشتغال عادي (مع توصيل بمحطة بعيدة المدى)




تشغيل / توقيف ON/OFF

- -- اضغط على زر (جهاز التباين الضوئي)، إذا كان التحميل مشتغلا، أدر الزر على وضعية التوقيف إذا كان التحميل غير مشتغل، و من تم أدر الزر على وضعية التشغيل.
 - اضغط على زر (القاطع الكهربائي كما هو موصل إلى المحطة بعيدة المدى) و واصل الضغط لمدة ثانيتين 2

تغيير مستوى الإنارة

- عندما يكون التحميل مشتغلا في (جهاز التباين الضوئي) أدر الزر نحو اليسار لينخفض مستوى الإنارة إلى أدنى مستوى، و أدر الزر نحو اليمين ليرتفع مستو الإنارة إلى أقصى مستوى. اضغط على زر (القاطع الكهربائي كما هو موصل إلى المحطة بعيدة المدى) و من تم اتركه بعد مرور ثانيتين 2، ليرتفع مستوى الإنارة إلى أعلى مستوى أو لينخفض إلى أدنى مستوى.

• اختيار نوع التحميل



- يستعمل زر القاطع الكهربائي الذي يدار نحو اليمين من أجل حمولة السعة أو حمولة مقاومة. - يستعمل زر القاطع الكهربائي الذي يدار نحو اليسار من أجل حمولة اقتيادية أو لحمولة مقاومة.

• ارشادات السلامة

يجب تركيب هذا المنتج وفقا لقواعد التركيب المعمول بها ويفضل أن يقوم بذلك كهربائي مؤهل. التركيب أو الاستعمال الخاطئ قد يؤدي إلى خطر التعرض إلى صدمة كهربائية أو الحريق. قبل إجراء التركيب، يرجى قراءة التعليمات وتركيب المنتج في الموقع الخاص به لا غير. لا تفتح ولا تفكك ولا تعدل ولا تغير من طبيعة المنتج باستثناء الحالات المتضمنة في الإرشادات. يجب أن يتم فتح وتصليح كافة منتجات Legrand حصريا من قبل مختصين مؤهلين ومعتمدين لدى Legrand.

يؤدي فتح أو تصليح المنتج بدون رخصة إلى إلغاء شامل لكافة المسئوليات والحقوق الخاصة بالاستبدال والضمانات.

لا تستعمل لواحق أو اكسسوارات أخرى غير لواحق أو اكسسوارات علامة Legrand.