



250HP						
	16 M	24 M	36 M	16/24/36 M		
3 P	3 386 00	3 386 03	3 386 06	3 386 50/53/56	3 384 50/53/56	
				 150 mm	 150 mm	
4P - 4P+Elcb	3 386 01	3 386 04	3 386 07	3 386 51/54/57	3 384 51/54/57	
				 200 mm	 200 mm	
250 HP						
	16 M	24 M	36 M	16/24/36 M		
3P - 4P - 4P+Elcb	3 386 21	3 386 24	3 386 27	3 386 71/74/77	3 382 71/72/73	
				 300 mm	 300 mm	





