



125HP						
	16 M	24 M	36 M	16/24/36 M		
3 P	3 385 00	3 385 03	3 385 06	3 385 50/53/56	3 383 50/53/56	
4P - 4P+Elcb	3 385 01	3 385 04	3 385 07	3 385 51/54/57	3 383 51/54/57	

125HP						
	16 M	24 M	36 M	16/24/36 M		
3 P	3 385 21	3 385 23	3 385 26	3 385 71/73/76	3 382 61/62/63/71/72/73	
4P - 4P+Elcb	3 385 21	3 385 24	3 385 27	3 385 71/74/77	3 382 61/62/63/71/72/73	

