

DPX ³ 160 3 P	3 396 20	16/24/36 M 3 383 50/53/56	250 HP 3 P	3 396 24	16/24/36 M 3 384 50/53/56
4 P/4P + ELCB	3 396 10	3 383 51/54/57	4 P/4 P + ELCB	3 396 16	3 384 51/54/57
DPX ³ 250 3 P	3 396 21	16/24/36 M 3 384 50/53/56	3 P	3 396 24	3 386 50/53/56
4 P/4 P + ELCB	3 396 11	3 384 51/54/57	4 P/4 P + ELCB	3 396 16	3 386 51/54/57
125 HP 3 P	3 396 23	16/24/36 M 3 383 50/53/56	630 3 P	3 396 22	16/24/36 M 3 387 50/53/56
4 P/4 P + ELCB	3 396 15	3 383 51/54/57	4 P/4 P + ELCB	3 396 12	3 387 51/54/57/58
3 P	3 396 23	3 385 50/53/56	DPX-IS 250	3 396 13	24/36 M 3 389 42/44
4 P/4 P + ELCB	3 396 15	3 385 51/54/57	DPX-IS 630	3 396 14	24/36 M 3 390 41/43

