



 -10°C ... +70°C	 2 x 1,5 W / 16 Ω 2 x 1,5 W / 8 Ω 2 x 2,5 W / 4 Ω	 (A2DP) 10 m	U, I 15 V= min. 4,5 mA max. 100 mA	 6 mm 2 x 1,5 mm²
 -5°C ... +40°C				

