









SIDE VIEW

63-160 A


CABLE GLAND
 ISO 16 max: 14
 ISO 21 max: 10
 ISO 25 max: 6
 ISO 40 max: 3
 ISO 50 max: 2

BACK VIEW




CABLE GLAND
 ISO 16 max: 14
 ISO 21 max: 9
 ISO 25 max: 6
 ISO 40 max: 2
 ISO 50 max: 1

SIDE VIEW




250 A

CABLE GLAND
 ISO 16 max: 17
 ISO 21 max: 13
 ISO 25 max: 7
 ISO 40 max: 3
 ISO 50 max: 2



BACK VIEW



CABLE GLAND
 ISO 16 max: 20
 ISO 21 max: 12
 ISO 25 max: 9
 ISO 40 max: 2
 ISO 50 max: 1




D

**63 A**

63 A




2 Nm

160 A

125 - 160 A



4 Nm

250 A






250 A




4 Nm

CH 4


D




BOTTOM VIEW





10




E



PE




FE



XCP

13



CLOSE











CH8
2 Nm

14

15

3 Nm
PH2

F



Quando si installa la cassetta sulla linea XCM basso (160/250/315A AL e 250/315/400A CU) sono da togliere

When installing the tap of box on the low XCM (160/250/315A AL and 250/315/400A CU) they must be removed

