

WPC Qi - EN 62479 - ICNIRP

-10°C ... +70°C	-5°C ... +35°C

14,5 mm max.

8 mm

U, I	
250 V~ 5 V~ 1.0 A / 3.0 A	<p>6 mm 2,5 mm<sup>2</sup></p>

**1**  
Unlock

**2**

**3**

**4**

**5**

**6**

**7**  
Lock

**7**  
Lock

