

⚠ Safety instructions

GB CA IN IE US SG

This product should be installed in compliance with installation rules, preferably by a qualified electrician. Incorrect installation and/or incorrect use can lead to risk of electric shock or fire.
 Before carrying out the installation, read the instructions and take account of the product's specific mounting location.
 Do not open up, dismantle, alter or modify the device except where specifically required to do so by the instructions.
 All Legrand products must be opened and repaired exclusively by personnel trained and approved by Legrand. Any unauthorised opening or repair completely cancels all liabilities and the rights to replacement and guarantees.
 Use only Legrand brand accessories.

Presentation


	 -20 °C ... +70 °C	 -5 °C ... +35 °C	 ≥40mm	 100-240V~ 50/60Hz	 8 mm 1...4mm ²
--	-----------------------	----------------------	-----------	--------------------------	----------------------------------



Technical characteristics

	R	L	C/L			C	L
1		2 	3 	4 	5 	6 Dimmable 	7 Dimmable LED
240V~ 50Hz	5...300 W	5... 300 VA	5... 300 VA	5... 200 VA	5...75 W ≤ 10 x 	5...200W ≤ 10 x 	5...75 W ≤ 10 x
100V~ 60Hz	5...150 W	5... 150 VA	5... 150 VA	5... 100 VA	5...37 W ≤ 10 x 	5...100W ≤ 10 x 	5...37 W ≤ 10 x




- 1** Incandescent lamp
- 2** Iron core transformer for extra low-voltage incandescent lamps(e.g.halogen)
- 3** Inductive ballast fluorescent lamp with compensator
- 4** Electronic step-down converter for extra low-voltage incandescent /fluorescent lamps
- 5** Fluorescent lamp **6** Dimmer CFL **7** Self-ballasted LED lamp

Wiring






Local+remote/auxiliary dimming:




Installation




Configuration

Factory reset




Operation


Min. brightness settings



CFL setting



Load type setting



C/R means for Capacitive load and Resistive load
L/R means for Inductive load and Resistive load