

Characteristics

				<p>U</p>	
	-10°C...+70°C	0°C...+35°C	≥35mm	100-240V~ 50/60Hz	8 mm 1~ 2,5 mm ²

	R	L	C/L		C	L	
240V~ 50/60Hz	5...300 W	5... 300 VA	5... 300 VA	5... 200 VA	5...75 W ≤ 10 x	5...200W ≤ 10 x	5...75 W ≤ 10 x
100V~ 50/60Hz	5...150 W	5... 150 VA	5... 150 VA	5... 100 VA	5...37 W ≤ 10 x	5...100W ≤ 10 x	5...37 W ≤ 10 x



