





















UTP STP	UTP		
	Cat 5e 55/59	-
	Cat 6 56/60 89	-
Cat 6A 57/61 58/62	





RJ45, 2 x RJ45, RJ11 + RJ45






RJ45 + RJ11

7 650 89



RJ11

4321



Ø 1,4 mm max.

26 AWG <math>< \varnothing < 21 \text{ AWG}</math>

