

	 - 10°C...+70°C	 40 mm		
	 -5°C ... +50°C	 ≥ 10 year	 00:00:25 ... 00:15:00 00:02:00 ... 02:00:00	 6 mm 1...2,5 mm <sup>2</sup>

8 A cos φ = 1 250V~	1840 W	400 VA	2x 58W 14μF	1000 W	400 W	250 VA	400 VA	400 VA	100 W

