

# SEANO™

7 650 47/48



|  |               |             |                |               |                          |
|--|---------------|-------------|----------------|---------------|--------------------------|
|  |               |             |                |               |                          |
|  | -10°C...+70°C | 0°C...+40°C | 250 V~<br>6 AX | 250 V~<br>6 A | <br>13 mm<br>2 x 1,5 mm² |

