







IP 55





IK 04





0 484 75

|                                                                                                                                                   |                                                                                                                                         |                                                                                                                                                                                         |
|---------------------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------|-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------|
|  <div><div>• 100 - 240 V~</div><div>• 100 - 240 Volt~</div></div> |  <div>-5°C / 30°C</div>                                |  <div><div>• PIR ( Passive Infra Red)</div><div>• IV</div><div>• IR</div><div>• PIR (인체감지)</div></div> |
|  <div>50 / 60 Hz</div>                                            |  <div>2000 lux</div>                                   |  <div><div>• Ø 8 m</div><div>• Ø 8 meter</div></div>                                                   |
|  <div>2 x 1.5mm<sup>2</sup> / 1 x 2.5mm<sup>2</sup></div>         |  <div>10s</div>                                        |  <div><div>• 12 m</div><div>• 12 meter</div></div>                                                     |
|  <div>7 mm</div>                                                  |  <div><div>• 1</div><div>• 2</div><div>• 3</div></div> |                                                                                                                                                                                         |

|                                                                                     |        |                                                                                     |        |                                                                                     |         |                                                                                     |             |                                                                                     |        |                                                                                     |       |                                                                                      |       |
|-------------------------------------------------------------------------------------|--------|-------------------------------------------------------------------------------------|--------|-------------------------------------------------------------------------------------|---------|-------------------------------------------------------------------------------------|-------------|-------------------------------------------------------------------------------------|--------|-------------------------------------------------------------------------------------|-------|--------------------------------------------------------------------------------------|-------|
|  |        |  |        |  |         |  |             |  |        |  |       |  |       |
| LED                                                                                 |        |  |        |  |         |  |             |  |        |  |       |  |       |
| 240 V~                                                                              | 350 VA | 3 A                                                                                 | 2000 W | 8.5 A                                                                               | 1000 VA | 4.3 A                                                                               | 10x(2x36 W) | 4.3 A                                                                               | I ≤ 2A | 500 VA                                                                              | 2.1 A | 1000 VA                                                                              | 4.3 A |
| 100 V~                                                                              | 175 VA |                                                                                     | 1000 W |                                                                                     | 500 VA  |                                                                                     | 5x(2x36 W)  |                                                                                     |        | 250 VA                                                                              |       | 500 VA                                                                               |       |

