



	<ul style="list-style-type: none"> • 100 - 240 V~ • 100 - 240 Volt~
	50 / 60 Hz
	2 x 1.5mm ² / 1 x 2.5mm ²
	8 mm
	-5°C / 30°C
	2000 LUX
	10s
	<ul style="list-style-type: none"> • PIR (Passive Infra Red) • IV • IR • PIR (인체감지)
	2.5 m
	<ul style="list-style-type: none"> • Ø 9 m • Ø 9 meter

LED							
240 V~	350 VA	3 A	2000 W	8,5 A	1000 VA	4,3 A	10x(2x36 W)
100 V~	175 VA		1000 W		500 VA		5x(2x36 W)
							I max. ≤ 2A
							500 VA
							2,1 A
							4,3 A







