



0 484 75

	<ul style="list-style-type: none"> <li>• 100 - 240 V~</li> <li>• 100 - 240 Volt~</li> </ul>		-5°C / 30°C		<ul style="list-style-type: none"> <li>• PIR ( Passive Infra Red)</li> <li>• IV</li> <li>• IR</li> <li>• PIR (인체감지)</li> </ul>
	50 / 60 Hz		2000 LUX		
	2 x 1.5mm <sup>2</sup> / 1 x 2.5mm <sup>2</sup>		10s		<ul style="list-style-type: none"> <li>• 24 m x 5 m</li> <li>• 24 meters x 5 meters</li> </ul>
	7 mm				

<b>LED</b>										
240 V~	350 VA	3 A	2000 W	1000 VA	4.3 A	10x(2x36 W)	4.3 A	500 VA	1000 VA	4.3 A
100 V~	175 VA		1000 W	500 VA		5x(2x36 W)		250 VA	500 VA	
			8.5 A					2.1 A		







