Audio/Video Web Server

F454

Description

Audio/Video Web Server for local and remote control of MY HOME applications using dedicated web pages.

The Web Server can also be used as a gateway for the management of the system using devices like PCs and Smartphones, and for virtual configuration, using a dedicated software.

Technical data

Power supply from SCS BUS: 18 – 27 Vdc

Absorption: 125 mA max (with active video interface)


Operating temperature: 5-35 °C

Dimensional data

6 DIN modules

Configuration

The Audio/Video Web Server should be configured using the MyHOME_Suite software, which is available to download from the website www.homesystems-legrandgroup.com.



Legend

- 1. RJ 45 for 10/100Mbit Ethernet LAN
- 2. Under the door are:
 - USB ports for PC configuration and Firmware update
 - RESET pushbutton
 - Serial connector RS232
- 3. User interface:
 - Speed: Connection speed; ON = 100 Mbit;

OFF = 10 Mbit

- Link: ON it indicates the presence of the Ethernet network
- System: when the power supply is connected, it comes on, goes off, and then comes on again, to indicate that the web server is working
- 4. 2-wire BUS for video door entry system connection
- 5. 2-wire BUS for burglar alarm system



