

	<p>17 mm</p>	<p>≤ 125 A</p> <p>10 - 50 mm²</p> <p>10 - 50 mm²</p> <p>10 - 70 mm²</p>
		<p>6.5 mm - Pz 3</p> <p>5.5 Nm</p>


