



1. USE

Power cord for server side locking.

Unique rotary mechanism on C13 plug that fits any standard C14 inlet to avoid accidental disconnection.

2. DESCRIPTION

Cat number	Color	Length (m)
6 441 00	Black	0.5
6 441 01	Black	1
6 441 02	Black	1.5
6 441 03	Black	2
6 441 06	Red	0.5
6 441 07	Red	1
6 441 08	Red	1.5
6 441 09	Red	2
6 441 12	Blue	0.5
6 441 13	Blue	1
6 441 14	Blue	1.5
6 441 15	Blue	2

3. TECHNICAL SPECIFICATIONS

SPECIFICATION	DESCRIPTION
High potential test voltage	2000VAC (1min 50Hz)
Rating	TUV : 10A 250VAC
Operation temperature	-20°C - +70°C
Flammability corresponding to	Cable (H05VVF) : IEC60332-1. Cat F2
Conductor size	1mm ²
Connector - End 1	C13 - IEC60320 1P+N+E with rotary locking mechanism Locking retention force : 100N
Connector - End 2	C14 - IEC60320 1P+N+E

4. STANDARDS AND APPROVALS

- IEC 60320-1
- EN 50525-2-11



4.1 REGULATORY APPROVALS

CE, UKCA, CMIM

RoHS directive (Restriction of Hazardous Substances)

REACH regulations (Registration, Evaluation, Authorisation & restriction of Chemicals).