NOW Heating/air conditioning room thermostat

Description

2-module stand-alone thermostat that records the room temperature and allows its adjustment.

It controls the temperature by means of an electronic sensor that controls an output relay with 1 x 5 (2) A potential free deviation contact.

It is also possible to adjust the antifreeze temperature, which automatically activates when the device is switched off.

On the front of the device are:

- the - and + temperature adjustment commands;

- the on/off command

- temperature/status display (automatically reduced brightness when in standby).

Technical data

Power supply Absorption Maximum cable section Operating temperature Temperature set-point Type of activation Pollution level Rated pulse voltage Contact output 110 - 240 Vac , 50/60Hz 2 W max 1 x 1.5mm2 0 - 40 °C 3 - 40 °C; increase of 0.5 °C 1BU 2 4 kV 5(2) A

Dimensional data

Size: 2 flush mounted modules.



Rear view

Front view



Legend

- 1. Backlight display
- 2. Temperature display
- 3. Lighting sensor
- ON / OFF key sets the system OFF anti-frost (7 °C) or heat-protection (35 °C) mode
- 5. Temperature setting indicator: appears when the temperature is being set
- 6. ON heating indicator
- 7. ON cooling indicator
- 8. Keys for temperature setting
- 9. Thermostat OFF indicator (see point 4)
- 10. Connection clamps (see diagrams)



ST-00001461-EN 01/

01/06/2023

KW4441 - KG4441 - KM4441

Configuration

Heating/cooling system mode setting



Touch the ON/OFF key (A) for more than 5 seconds. The current mode (H = heating, C = cooling) is displayed. Touch the + or - keys (B) to modify it.

Temperature format setting

Temperature calibration

Display brightness adjustment







Touch both the + and - keys (A) for more than 5 seconds. The current temperature format is displayed (C = degrees Celsius, F = degrees Fahrenheit). Touch the + or – keys to modify it.

Touch both the ON/OFF (A) and + (B) keys for more than 5 seconds. The deviation between the measured temperature and the temperature displayed by the thermostat is displayed. Touch the + or – keys to modify it.

Note: wait a few minutes before checking the measured room temperature again.

Touch ON/OFF (A) and - (B) at the same time for more than 5 seconds to display the brightness adjustment setting. Touch + or - to adjust the brightness as desired.

- The following settings are available:
- A2: automatic adjustment, the display is always on
- A1: automatic adjustment, display can turn off
- 0...3: fixed adjustment. When set to 0, in standby the display switches off completely.



ST-00001461-EN

01/06/2023

2

Wiring diagrams

System only for heating with clean contact (e.g. boiler agreement)



System only for heating with load to be controlled to the network voltage (e.g. 230Vac solenoid valve)



Heating and cooling with floor system



Heating and cooling with different systems



