

MWS1A-C-PRM-LV | PRM switching, long range, IP40, ceiling, back box mounted, microwave, presence detector, low voltage



Key Product Features:


- Presence detection
- Low voltage
- Easily setup using the optional UHS5 infrared handset – no need to remove unit to re-program
- Detection range of up to 10 metres
- Suitable for heating and ventilation applications
- Compatible with European back boxes
- Fixing screw cap covers – smooth plate finish
- 5 year warranty

Key Functions:


- User handset available to control on/off and lux levels
- Suitable for all lighting types

Detection pattern


high < sensitivity > low



Dimensions (mm)










Technical Data

Part Code	MWS1A-C-PRM-LV
Weight	0.100kg
Supply Voltage AC	10–26.5 VAC
Supply voltage DC	11.5–36 VDC
Power consumption parasitic	712mW
Terminal capacity	2.5mm ²
Min load	100mA
Max load:	
Incandescent lighting	10A
Fluorescent lighting	10A
Compact fluorescent lighting	10A
LED lighting	10A
Resistive heaters	16A
Time out range	10 seconds to 99 minutes
Max power factor correction capacitance	40µF
Working temperature range	-10 to 50°C
Humidity	5 to 95% non-condensing
Material (casing)	Flame retardant ABS
Insulation class	Class 2
Microwave frequency	10.587GHz
IP rating	40
Compliance	 EMC-2004/108/EC LVD-2006/95/EC

Accessories and Associated Products

Part Number	Description
 UHS5	Compact, programming/commissioning handset

 <p>www.cpelectronics.co.uk</p>	<p>CP Electronics A Business unit of Legrand Electric Limited, Brent Crescent, London NW10 7XR, UK t. +44 (0)333 900 0671 info@cpelectronics.co.uk</p> <p>connect with us    </p>	<p>Important notice: This device should be installed by a qualified electrician in accordance with the latest edition of the IEE Wiring Regulations and the applicable Building Regulations.</p> <p>Due to our policy of continual product improvement CP Electronics reserves the right to alter the specification of this product without prior notice.</p> <div style="text-align: right;">   </div>
--------------------------------------------------------------------------------------------------------------------	-----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------	----------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------------