


Technical sheet: F6023B

2 P + E grey plastic extension 20 A

87045 LIMOGES Cedex Telephone: +33 5 55 06 87 87 - Fax: +33 5 55 06 88 88 C

^{8 88} Cat. No(s): 550 03

Date: 6.03.97



1. CHARACTERISTICS

For power supply of Class I appliances

for cable 15 mm max. diameter

Maximum continuous temperature (without stress): 90 °C

Material: polypropylene

Resistance to chemicals

Resistance to chemical agents of the plastic body at ambient temperature

Acids (acetic, boric, oxalic, lactic, phosphoric)	good
Bases (sodium carbonate, ammonium nitrate)	good
Brine and potash	good
Alcohol solutions (ethanol)	good
Detergents	good
Glycerine	good
Nitric acid	poor
Supergrade type petrol	average
Diesel	good

2. CONFORMITY TO FRENCH STANDARDS (USE)

3. PROTECTION INDEX: IP20