


# XL<sup>3</sup> S 160

## technical characteristics

### ■ Dimensions of surface mounting cabinets




#### 24-module cabinets

| Cat.Nos  | H (mm) | W (mm) | D (mm) |
|----------|--------|--------|--------|
| 3 372 02 | 440    | 595    | 135    |
| 3 372 03 | 590    | 595    | 135    |
| 3 372 04 | 740    | 595    | 135    |
| 3 372 05 | 890    | 595    | 135    |
| 3 372 06 | 1040   | 595    | 135    |
| 3 372 07 | 1190   | 595    | 135    |
| 3 372 08 | 1340   | 595    | 135    |

#### 36-module cabinets

| Cat.Nos  | H (mm) | W (mm) | D (mm) |
|----------|--------|--------|--------|
| 3 372 14 | 740    | 810    | 135    |
| 3 372 15 | 890    | 810    | 135    |
| 3 372 16 | 1040   | 810    | 135    |
| 3 372 17 | 1190   | 810    | 135    |
| 3 372 18 | 1340   | 810    | 135    |

### ■ Dimensions of flush-mounting cabinets



#### 24-module cabinets

| Cat.Nos  | H1 (mm) | H2 (mm) | W (mm) |
|----------|---------|---------|--------|
| 3 372 22 | 512     | 440     | 667    |
| 3 372 23 | 662     | 590     | 667    |
| 3 372 24 | 812     | 740     | 667    |
| 3 372 25 | 962     | 890     | 667    |
| 3 372 26 | 1112    | 1040    | 667    |
| 3 372 27 | 1262    | 1190    | 667    |
| 3 372 28 | 1412    | 1340    | 667    |

#### 36-module cabinets

| Cat.Nos  | H1 (mm) | H2 (mm) | W (mm) |
|----------|---------|---------|--------|
| 3 372 34 | 812     | 740     | 883    |
| 3 372 35 | 962     | 890     | 883    |
| 3 372 36 | 1112    | 1040    | 883    |
| 3 372 37 | 1262    | 1190    | 883    |
| 3 372 38 | 1412    | 1340    | 883    |