

XL³ S 4000
isolating busbar supports selection chart (continued)

Max. In (A)	Flat copper bars					C-section aluminium busbars				
	400	800	3000	4000		630	1600	3200		
Mounting	Supports									
XL³ S 4000										
	D: 400	3 399 00 + 3 397 34			3 399 20/23 + 3 399 36/37/38/39 ⁽³⁾			3 399 02/03 + 3 397 34	3 399 20/23 + 3 399 40 ⁽³⁾	3 399 31 ⁽³⁾
	D: 600	Front access ⁽¹⁾ 3 399 00 + 3 397 35	3 399 06 + 3 397 35	3 399 21/23 + 3 399 36/37/38/39				3 399 02/03 + 3 397 35	3 399 21/23 + 3 399 40	3 399 32
	Rear access ⁽²⁾ 3 399 00 + 3 397 35	3 399 06 + 3 397 35	3 399 21/23 + 3 399 36/37/38/39					3 399 02/03 + 3 397 35	3 399 21/23 + 3 399 40	3 399 32
	D: 800	Front access ⁽¹⁾ 3 399 00 + 3 397 36	3 399 06 + 3 397 36	3 399 22/23 + 3 399 36/37/38/39				3 399 02/03 + 3 397 36	3 399 22/23 + 3 399 40	3 399 33
	Rear access ⁽²⁾ 3 399 00 + 3 397 36	3 399 06 + 3 397 36	3 399 22/23 + 3 399 36/37/38/39					3 399 02/03 + 3 397 36	3 399 22/23 + 3 399 40	3 399 33
	D: 400	3 399 00 + 3 397 34			3 399 20/23 + 3 399 36/37/38/39 ⁽³⁾			3 399 02/03 + 3 397 34	3 399 20/23 + 3 399 40 ⁽³⁾	3 399 31 ⁽³⁾
	D: 600	Front access ⁽¹⁾ 3 399 00 + 3 397 35	3 399 06 + 3 397 35	3 399 21/23 + 3 399 36/37/38/39				3 399 02/03 + 3 397 35	3 399 21/23 + 3 399 40	3 399 32
	Rear access ⁽²⁾ 3 399 00 + 3 397 35	3 399 06 + 3 397 35	3 399 21/23 + 3 399 36/37/38/39	3 399 29/30				3 399 02/03 + 3 397 35	3 399 21/23 + 3 399 40	3 399 32
	D: 400	3 399 00 + 3 397 34			3 399 20/23 + 3 399 36/37/38/39 ⁽³⁾			3 399 02/03 + 3 397 34	3 399 20/23 + 3 399 40 ⁽³⁾	3 399 31 ⁽³⁾
	D: 600	Front access ⁽¹⁾ 3 399 00 + 3 397 35	3 399 06 + 3 397 35	3 399 21/23 + 3 399 36/37/38/39				3 399 02/03 + 3 397 35	3 399 21/23 + 3 399 40	3 399 32
	Rear access ⁽²⁾ 3 399 00 + 3 397 35	3 399 06 + 3 397 35	3 399 21/23 + 3 399 36/37/38/39	3 399 29/30				3 399 02/03 + 3 397 35	3 399 21/23 + 3 399 40	3 399 32
	D: 800	Front access ⁽¹⁾ 3 399 00 + 3 397 36	3 399 06 + 3 397 36	3 399 22/23 + 3 399 36/37/38/39				3 399 02/03 + 3 397 36	3 399 22/23 + 3 399 40	3 399 33
	Rear access ⁽²⁾ 3 399 00 + 3 397 36	3 399 06 + 3 397 36	3 399 22/23 + 3 399 36/37/38/39	3 399 29/30				3 399 02/03 + 3 397 36	3 399 22/23 + 3 399 40	3 399 33
	D: 600 mm				3 399 20/23 + 3 399 36/37/38/39			3 399 02/03 + 3 397 34	3 399 20/23 + 3 399 40	
	D: 800 mm				3 399 06 + 3 397 35	3 399 21/23 + 3 399 36/37/38/39		3 399 02/03 + 3 397 35	3 399 21/23 + 3 399 40	3 399 25/27 + 3 399 40
	D: 600 mm				3 399 06 + 3 397 35					
	D: 800 mm				3 399 06 + 3 397 36					
	W: 16 modules							3 399 04/05 + 3 397 80		
	W: 24 modules		3 399 01 + 3 379 81					3 399 04/05 + 3 379 81		
	W: 36 modules		3 399 01 + 3 379 82					3 399 04/05 + 3 379 82		
	W: 16 modules / 450 mm				3 399 20/23 + 3 399 36/37/38/39 ⁽⁶⁾			3 399 20/23 + 3 399 40 ⁽⁶⁾		
	W: 24 modules				3 399 06 + 3 397 35	3 399 21/23 + 3 399 36/37/38/39 ⁽⁶⁾		3 399 21/23 + 3 399 40 ⁽⁶⁾		3 399 25/27 + 3 399 40 ⁽⁶⁾
	W: 36 modules				3 399 06 + 3 397 36	3 399 22/23 + 3 399 36/37/38/39 ⁽⁶⁾		3 399 22/23 + 3 399 40 ⁽⁶⁾		3 399 26/27 + 3 399 40 ⁽⁶⁾
	W: 16 modules / 450 mm									
	Internal cable sleeve				3 399 20 + 3 399 36/37/38/39 + 3 397 36 x 2			3 399 20 + 3 399 40 + 3 397 36 x 2		3 399 25 + 3 399 40 + 3 397 36 x 2
	Internal cable sleeve with intermediate upright at back				3 399 20 + 3 399 36/37/38/39 + 3 397 37 x 2			3 399 20 + 3 399 40 + 3 397 37 x 2		3 399 25 + 3 399 40 + 3 397 37 x 2
	Cable sleeve W: 350 mm				3 399 20 + 3 399 36/37/38/39 + 3 397 30 x 2	3 399 29 + 3 397 30 x 2		3 399 20 + 3 399 40 + 3 397 30 x 2		3 399 25 + 3 399 40 + 3 397 30 x 2
	Cable sleeve W: 450 mm / 16 modules				3 399 20 + 3 399 36/37/38/39 + 3 397 31 x 2	3 399 29 + 3 397 31 x 2		3 399 20 + 3 399 40 + 3 397 31 x 2		3 399 25 + 3 399 40 + 3 397 31 x 2
	W: 24 modules				3 399 20 + 3 399 36/37/38/39 + 3 397 35 x 2	3 399 29 + 3 397 35 x 2		3 399 20 + 3 399 40 + 3 397 35 x 2		3 399 25 + 3 399 40 + 3 397 35 x 2
	W: 36 modules				3 399 20 + 3 399 36/37/38/39 + 3 397 36 x 2	3 399 29 + 3 397 36 x 2		3 399 20 + 3 399 40 + 3 397 36 x 2		3 399 25 + 3 399 40 + 3 397 36 x 2

1: The horizontal main busbar is in the front position in the cabinet. The vertical busbars are therefore accessible from the front of the enclosure, behind the front plates (mainly by the cable sleeves).
 2: The horizontal main busbar is at the back of the enclosure. The vertical busbars are accessible from the back of the enclosure by removing the rear panels.

3: Connection possible only with a horizontal top or bottom busbar made of C-section aluminium bars;
 4: Partial chassis; 5: Mounting behind the crosspiece of the central upright

6: Mounting on crosspieces in the enclosure

7: Mounting behind functional uprights

8: Except depth 400 mm;

9: The 2 sets of bars are placed one above the other in the height of the cabinet