

Arteor™

wireless power chargers



Arteor™

wireless power chargers



5 720 76



0 775 80 supplied with sticker



0 775 99

Wireless power chargers for fast charging a smartphone with a Qi receiver
 Power supply standby mode consumption < 0.07%
 Conform to the Qi WPC standard (Wireless Power Consortium): certified for professional Qi 1.2.3 projects
 Conform to EN 62479 standard (EMF emissions)
 Conform to ICNIRP specifications (health protection)
 Do not interfere with other wireless signals (Zigbee, TNT, GSM, 4G, etc)

Pack	Cat.Nos	Qi wireless chargers - for integration into the furniture
		<p>Specially designed for mounting horizontally on furniture. For meeting rooms, offices, public areas, etc 80 mm drilling diameter, Aluminium colour Extra-slim with thickness < 1.5 mm Supplied with identification sticker diameter 85/110 mm, 2.5 m cord, fixing base and cable ties 110-240 V universal power supply Plugs conforming to European, BS, US, Australian/ Chinese standards</p>
1	0 775 80	5 W - IP 44 / IK 08 charger
1	0 776 00	15 W - IP 44 / IK 06 charger



Pack	Cat.Nos	Flush-mounted wireless chargers - for public area
1	0 775 99	<p>1 A - 5 V/5 W wireless charger. Specially designed for public buildings, passageways or transit areas, swimming pools, etc. IK 08 - IP 66 - Class II SELV Comes with 2 induction antennae for fast smartphone charging. Recognition area: 50 x 80 mm Plate at an angle of 10° with non-slip coating to hold the terminal safely in place during charging Screws onto flush-mounting box with 60 mm fixing centres, min. depth 40 mm, French, German or British standard. Can also be fixed in at 4 points. Can be mounted on rectangular boxes and outdoors 110/230 VA Phase + Neutral power supply Mechanism supplied with cover plate, attached with 2 Torx screws at the side</p> <p>● Aluminium colour Dimensions: 141 x 95 x 51 mm 2 x 2.5 mm² terminals</p>



Pack	Cat.Nos	Wireless charger + Type-A USB - Arteor version
1	5 720 76	<p>1 A - 5 V/5 W charger with one 3 A/12 W USB port to power a second device Specially designed for work areas For installation in flush-mounting box, surface mounting box, workstation kit, column module, multi-outlet extension for offices, etc To be fitted with a support and a plate depending on the selection of the wiring accessories ranges Comes with 2 induction antennae for fast intuitive smartphone charging. Recognition area: 50 x 80 mm Plate at an angle of 10° with non-slip coating to hold the terminal safely in place during charging Dimensions: 136.5 x 70 x 56.5 mm Anti-theft lock function Can be mounted in multiple horizontal positions</p> <p>○ White with metallic finishing plate 2 x 2.5 mm² terminals</p>



Wireless power charging

A Legrand innovation for fast, easy charging


Using wireless energy transfer
 No need for cords and connectors

An open international standard: Qi

Wireless Power Consortium: 270 members, ensuring interoperability with induction-compatible phones
 Qi: global standard adopted by vehicle manufacturers and cafés/hotels/restaurants
 Products certified for professional Qi 1.2.3 projects

Ergonomically designed to suit different environments


Horizontal charging on furniture



Insertion in an 80 mm diameter cut-out / Fixed info furniture
 External power supply with 2.5 m cord

Vertical charging on a wall in public areas (semi-flush-mounted)

Ideal for indoor or outdoor locations



Excellent resistance to impacts (IK 08) and adverse weather conditions (IP 66)
 Can be fixed directly on the flush-mounting box or for extra strength drilled with anchor bolts

Charging in Arteor environment

With induction and 2.4 A / 12 W USB socket

