

Belanko™

socket outlets (continued)



6 170 60



6 170 65



6 170 69



6 171 49

Colour: White T084. Material: Thermoplastic with glossy finish
 Dimensions: 86 x 86 x 9.5 mm (1 gang) / 86 x 146 x 9.5 mm (2 gang). Supplied with 2 screws M3.5 for BS boxes

Pack	Cat.Nos	Euro/US standard socket outlets - 16 A - 250 V~ / 15 A - 127 V~
10	6 170 60	1 gang - 2P
10	6 170 61	1 gang - 2P + 10 AX switch
10	6 170 62	1 gang - 2 x 2P
10	6 170 63	1 gang - 2P+E
10	6 170 64 N	1 gang - 2 x 2P+E

Pack	Cat.Nos	US standard socket outlet - 15 A - 127 V~
10	6 170 65	1 gang - 2P+E
10	6 170 56	German standard socket outlet - 16 A - 250 V~ 1 gang - 2P+E with shutters for child protection
10	6 170 67	Multistandard switched socket outlets 1 gang
4	6 170 69	2 gang

Pack	Cat.Nos	Multistandard switched socket outlets 16 A - 250 V~ / 15 A - 127 V~ with USB charger
1	6 170 59 N	Shuttered for child safety USB charger conform to IEC 60950-1 2P+E - 1 gang USB Type-A 2.4 A - 5 V~ - 12 W Consumption in passive mode < 0.08 W
1	6 171 49 N	2 x 2P+E - 2 gang USB Type-A + Type-C™ 3 A - 5 V~ 15 W Consumption in passive mode < 0.08 W