

Belanko™

fused connection units, cable outlets, surface-mounting boxes, plates and blanking plates



6 170 81



6 170 85



6 171 36 + 6 170 42



6 133 50



6 171 55



6 171 51

Pack	Cat.Nos	Fused connection units
10	6 170 80	13 A Conform to BS 1363-4 Unswitched + cord outlet
10	6 170 81	Switched + cord outlet
10	6 170 82	Switched + neon + cord outlet
Cable outlets		
10	6 170 85	Conform to BS 5733 20 A - 250 V~
10	6 170 86	45 A - 250 V~
Fixing accessories		
100	6 171 30	Screw caps
2	6 171 36	Splash-proof cover Mainly for socket protection IP 55 with or without plug engaged Space inside : 86 x 86 mm (for Belanko, Mallia and Synergy products)
Surface-mounting boxes		
10	6 133 49	Conform to BS 5733 depth 35 mm Architrave surface box
8	6 133 50	1 gang surface box - 86 x 86 mm Supplied with earth terminal
4	6 133 51	2 gang surface box - 86 x 146 mm Supplied with earth terminal

Pack	Cat.Nos	Plates
5	6 171 50	1 gang - horizontal ● Beige ● Taupe
5	6 171 55	
5	6 171 51	1 gang - vertical ● Beige ● Taupe
5	6 171 56	
5	6 171 52	2 gang - horizontal ● Beige ● Taupe
5	6 171 57	
5	6 171 53	2 gang - vertical ● Beige ● Taupe
5	6 171 58	
Blanking plates		
10	6 171 28	Conform to BS 5733 1 gang
5	6 171 29	2 gang
Arteor adaptor		
10	6 171 32	1 gang
Active Power Compensator		
1	N 0 401 49	Allows 2-wire electronic switches without neutral to be compatible with all loads (LED, fluocompact)

