

Synergy™

Grid modules - decorative rockers, white and anthracite rockers without marking



8 326 00 8 326 06 8 326 12 7 355 00 7 354 21 7 354 50 7 353 65

Front plate selection charts p. 596

Pack	Cat.Nos	Single pole switches 10 AX - 250 V~ - decorative rockers
1	8 326 00	1-way switches ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 326 06	
1	8 326 12	
1	8 326 01	2-way switches ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 326 07	
1	8 326 13	
1	8 326 02	Intermediate switches ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 326 08	
1	8 326 14	
		Single pole switches 20 AX - 250 V~ - decorative rockers
1	8 326 03	1-way switches ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 326 09	
1	8 326 15	
1	8 326 04	2-way switches ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 326 10	
1	8 326 16	
1	8 326 05	2-way retractive centre off switches ● Brushed stainless steel ● Polished stainless steel ● Glossy gold
1	8 326 11	
1	8 326 17	
		Single pole switches 10 AX - 250 V~
10	White 7 354 00	Conform to BS EN 60669-1 1 way 1 way + neon 2 way Intermediate 2-way push switch 2-way push switch marked "BELL"
10	Anthracite 7 355 00	
10	White 7 354 01	
10	Anthracite 7 355 01	
10	White 7 354 03	
10	Anthracite 7 355 03	
10	White 7 354 07	
10	Anthracite 7 355 07	
10	White 7 354 05	Conform to BS EN 60669-1 1 way 1 way + neon 2 way Intermediate 2-way centre off 2-way retractive centre off 2-way push switch
10	Anthracite 7 355 05	
10	White 7 354 06	
10	Anthracite 7 355 06	
10	White 7 354 10	
10	Anthracite 7 355 10	
10	White 7 354 11	
10	Anthracite 7 355 11	
10	White 7 354 12	Conform to BS EN 60669-1 Key supplied 2-way 2-way retractive centre off
10	Anthracite 7 355 12	
10	White 7 354 18	
10	Anthracite 7 355 18	
10	White 7 354 13	
10	Anthracite 7 355 13	
10	White 7 354 14	
10	Anthracite 7 355 14	
10	White 7 354 15	Conform to BS EN 60669-1 Key supplied 2-way 2-way retractive centre off
10	Anthracite 7 355 15	
10	White 7 354 16	
10	Anthracite 7 355 16	
10	White 7 354 17	
10	Anthracite 7 355 17	

Pack	Cat.Nos	Double pole switches 20 AX - 250 V~
10	White 7 354 20	Conform to BS EN 60669-1 Switch Switch + neon Push to make Push to break
10	Anthracite 7 355 20	
10	White 7 354 21	
10	Anthracite 7 355 21	
10	White 7 354 22	Conform to BS EN 60669-1 Key supplied Key switch Key switch + neon
10	Anthracite 7 355 22	
10	White 7 354 25	
10	Anthracite 7 355 25	
10	White 7 354 23	Conform to BS EN 60669-1 Key supplied Key switch Key switch + neon
10	Anthracite 7 355 23	
10	White 7 354 24	Conform to BS EN 60669-1 2-way - 300 W - push dimmer
10	Anthracite 7 355 24	
1	White 7 354 46	Conform to BS EN 60669-2-1 2-way - 300 W - push dimmer
1	Anthracite 7 355 46	
1	White 7 354 47	Time delay switch 300 W
1	Anthracite 7 355 47	
1	White 7 354 50	BT master BT secondary
1	Anthracite 7 355 50	
1	White 7 354 51	RJ 45 - 8 contacts
1	Anthracite 7 355 51	
10	White 7 352 56	Screened TV single, male Screened TV-SAT
10	Anthracite 7 353 56	
10	White 7 354 40	Hi-Fi loudspeaker socket
10	Anthracite 7 355 40	
10	White 7 354 41	Fuse carrier
10	Anthracite 7 355 41	
10	White 7 352 65	Indicator - green neon Indicator - red neon
10	Anthracite 7 353 65	
10	White 7 350 30	Blanking plate
10	Anthracite 7 351 30	
10	White 7 350 62	Blanking plate
10	Anthracite 7 351 62	
20	White 7 354 36	