

URASPOT

LED emergency lighting spotlights for ceiling



URASPOT

LED emergency lighting spotlights for ceiling



Non-maintained self-contained emergency lighting units
 Certified to IEC and EN 60598-2-22 standards
 High power LED with high performance lens specially designed:
 - to optimize lighting distribution on the floor
 - to increase spacing for installation
 Low consumption switching power supply
 Duration: 1 and 3 hours
 Ni-Cd batteries
 Charge monitor with green LED
 Recharging time: 18 hours
 Power supply: 230 V~ ± 10% - 50/60 Hz. Class II
 IP 40 - IK 04
 Screwless terminal blocks: 2 x 1,5 mm²

Pack	Cat.Nos	Standard luminaires non-maintained (NM)
1	6 618 60	200 lm - 1 h
1	6 618 61	For corridors and escape routes
		For open areas and antipanic
1	6 618 64	100 lm - 3 h
1	6 618 65	For corridors and escape routes
		For open areas and antipanic

Spacing tables (to provide 1lux on the floor)

For corridors and escape routes


Height (m)	Spacing (in m)				
2	6.97	15.88	14.48	5.39	1.87
2.5	8.18	18.32	16.94	5.65	1.88
3	9.23	20.70	19.19	5.35	1.80
3.5	10.16	23.11	20.73	5.34	1.78
4	10.42	25.29	21.39	5.24	1.54

For open areas and antipanic


Height (m)	Spacing (in m)				
2	3.33	8.40	8.40	8.40	3.33
2.5	3.57	9.26	9.26	9.26	3.57
3	3.70	9.89	9.89	9.89	3.70
3.5	3.75	10.31	10.31	10.31	3.75
4	3.73	10.62	10.62	10.62	3.73

Photometric curves

6 618 60/64



6 618 61/65



Dimensions (mm)

