



# 19" BATI-RACK




## 19" Bati-rack



 **Technical characteristics p. 793**

Pack	Cat.Nos	<b>19" Bati-rack</b>					
		For housing 19" equipment in an air conditioned, secure, dust-free environment Comprises 2 or 4 x 19" uprights With levelling feet The 4-upright bati-rack takes shelves for enclosures depth 800 mm Supplied ready for assembly RAL 7035					
1	0 463 95	Capacity	Height <sup>(1)</sup>	Width	Depth	Loading capacity (kg)	Number of uprights
1	0 463 96	42 U	1965	550	640	300	2
		<b>Cable management sleeve</b>					
		Closed vertical feedthrough Reversible door For fixing on the right or left on the 19" uprights RAL 7035					
1	0 463 97	Sleeve					
		<b>Roof</b>					
1	0 464 98	Roof for 4-upright bati-rack 535 x 600 mm					
		<b>Set of 4 casters</b>					
1	0 464 99	For bati-rack Loading capacity on the 4 casters: 340 kg					
		<b>Shelves</b>					
		Black RAL 9005					
		<b>Screw fixing on 2 x 19" uprights</b>					
		Height 2 U					
1	6 465 01	Max. load: 15 kg					
1	6 465 02	Shelf depth 200 mm					
		<b>Screw fixing on 4 x 19" uprights</b>					
		Height 1 U					
1	6 465 06	Fixed shelf depth 625 mm. Max load: 50 kg					
1	6 465 09	Telescopic shelf depth 625 mm. Max load: 30 kg					
		<b>19" management panels</b>					
		Fitted with cable guide rings					
1	6 465 20	1 U					
1	6 465 21	2 U					



▶ Full access to the wiring



▶ Takes cable management sleeves for a perfect finish

1: Without adjustment levelling feet (+ 27 to 42 mm with feet)