

DLPlus mini-trunking: wiring accessories frames

BODIES	MOSAIC FRAMES									
	Installation at the end of the mini-trunking ⁽¹⁾					Installation alongside the mini-trunking ⁽¹⁾				
Size and shape	2 modules ⁽²⁾	4 modules ⁽³⁾	6 modules ⁽⁴⁾	2 x 4 modules ⁽⁵⁾	3 x 4 modules ⁽⁶⁾	2 modules ⁽²⁾	4 modules ⁽³⁾	6 modules ⁽⁴⁾	2 x 4 modules ⁽⁵⁾	3 x 4 modules ⁽⁶⁾
	1 frame + 1 adaptor					1 frame + 1 adaptor				
20 x 12.5 	0 316 11 0 316 40	0 316 13 0 316 40	0 316 14 0 316 40	0 316 21 0 316 40	0 316 22 0 316 40	0 316 11 0 317 01	0 316 13 0 317 02	0 316 14 0 317 03	0 316 21 0 317 02	0 316 22 0 317 03
32 x 12.5 	0 316 11 0 316 41	0 316 13 0 316 41	0 316 14 0 316 41	0 316 21 0 316 41	0 316 22 0 316 41	0 316 11 0 317 01	0 316 13 0 317 02	0 316 14 0 317 03	0 316 21 0 317 02	0 316 22 0 317 03
32 x 16 	0 316 11 0 316 41	0 316 13 0 316 41	0 316 14 0 316 41	0 316 21 0 316 41	0 316 22 0 316 41	0 316 11 0 317 04	0 316 13 0 317 05	0 316 14 0 317 06	0 316 21 0 317 05	0 316 22 0 317 06
40 x 20 	0 316 11 0 316 47	0 316 13 0 316 47	0 316 14 0 316 47	0 316 21 0 316 47	0 316 22 0 316 47	0 316 11 0 317 07	0 316 13 0 317 08	0 316 14 0 317 09	0 316 21 0 317 08	0 316 22 0 317 09
60 x 20 	0 316 11 0 316 45	0 316 13 0 316 45	0 316 14 0 316 45	0 316 21 0 316 45	0 316 22 0 316 45	0 316 11 0 317 07	0 316 13 0 317 08	0 316 14 0 317 09	0 316 21 0 317 08	0 316 22 0 317 09
75 x 20 	-	0 316 13 0 316 48	0 316 14 0 316 48	0 316 21 0 316 48	0 316 22 0 316 48	0 316 11 0 317 07	0 316 13 0 317 08	0 316 14 0 317 09	0 316 21 0 317 08	0 316 22 0 317 09

1: Use with Mosaic socket outlet
2: Frame dimensions (2 modules): 127 x 74 x 60 mm
3: Frame dimensions (4 modules): 172 x 74 x 60 mm

4: Frame dimensions (6 modules): 217 x 74 x 60 mm
5: Frame dimensions (2x4 modules): 162 x 167 x 60 mm
6: Frame dimensions (2x4 modules): 228 x 74 x 60 mm

BODIES	Special surface mounting frames for wiring accessories (p. 798-800)		Surface mounting frames for 60 mm fixing centres wiring accessories (p. 801)		
	Installation alongside the mini-trunking		Installation alongside the mini-trunking		
Size and shape					
	1 gang for horizontal or vertical	2 gang for horizontal or vertical	1 gang for horizontal or vertical	2 gang for horizontal or vertical	3 gang for horizontal or vertical
20 x 12.5 	0 314 04	0 314 14	0 316 94	0 316 95	0 316 96
32 x 12.5 	0 314 04	0 314 14	0 316 94	0 316 95	0 316 96
32 x 16 	0 314 56	0 314 66	0 316 94	0 316 95	0 316 96
40 x 20 	0 314 08	0 314 18	0 316 94	0 316 95	0 316 96
60 x 20 	0 314 08	0 314 18	0 316 94	0 316 95	0 316 96
75 x 20 	0 314 08	0 314 18	0 316 94	0 316 95	0 316 96