

# Flexible cover snap-on DLP trunking

routing sections and accessories

# Mechanisms for flexible cover snap-on DLP trunking


Number of compartments	Cover width (mm)	Cross-section (mm)	TRUNKING				ACCESSORIES			ANGLES			JUNCTIONS & ADAPTOR										
			Monobloc: body + cover <sup>(1)</sup>	Extra cover	Extra partition (divider)	Fishplate body joint	Stick-on body joint	Cover joint	End cap	Internal angles <sup>(2)</sup>	External angles	Flat angles	Flat junctions with width 80 mm	Flat junctions with width 105 mm	Angled junctions 85/105/130 mm	Junction with floor duct 50 x 12/ 92 x 20	Adaptor for modular wiring accessories						
<b>FLEXIBLE COVER SNAP-ON TRUNKING - 45 mm cover</b>																							
	45	50 x 80	● 0 757 50 2 m	0 757 79	0 756 09	-	0 757 80	0 757 85	0 757 55	0 757 60	0 757 65	0 757 70					0 757 75	-	-	-	-		
			○ 0 756 01 2 m	0 756 08	0 756 09	0 756 61	0 756 66	0 756 69	0 756 11	0 756 21	0 756 31	0 756 41						0 756 71	-	0 756 81 + 0 756 21	0 756 88	0 310 69	
			○ 0 110 20 2.5 m	0 756 08	0 756 09	0 756 61	0 756 66	0 756 69	0 756 11	0 756 21	0 756 31	0 756 41						0 756 71	-	0 756 81 + 0 756 21	0 756 88	0 310 69	
			Antimicrobial ○ 0 757 00 2 m	0 757 29	0 756 09	-	0 757 30	0 757 35	0 757 05	0 757 10	0 757 15	0 757 20						0 757 25	-	-	-	-	-
			● 0 758 00 2 m	0 758 29	0 756 09	0 758 30	0 758 33	0 758 35	0 758 05	0 758 10	0 758 15	0 758 20						0 758 25	-	-	-	-	-
	45	50 x 105	0 756 02	0 756 08	0 756 09	0 756 62	0 756 67	0 756 69	0 756 12	0 756 22	0 756 32	0 756 42				0 756 72	0 756 76	0 756 81 + 0 756 22	0 756 88	0 310 69			
	45 45	50 x 130	● 0 757 52 2 m	0 757 79	-	-	0 757 80	2 x 0 757 85	0 757 57	0 757 62	0 757 67	0 757 72					0 757 75	-	-	-	-		
			○ 0 756 03 2 m	0 756 08	-	0 756 61	0 756 66	2 x 0 756 69	0 756 13	0 756 23	0 756 33	0 756 43					0 756 71	0 756 75	0 756 81 + 0 756 23	0 756 88	0 310 69		
			○ 0 110 22 2.5 m	0 756 08	-	0 756 61	0 756 66	2 x 0 756 69	0 756 13	0 756 23	0 756 33	0 756 43					0 756 71	0 756 75	0 756 81 + 0 756 23	0 756 88	0 310 69		
			Antimicrobial ○ 0 757 02 2 m	0 757 29	-	-	0 757 30	2 x 0 757 35	0 757 07	0 757 12	0 757 17	0 757 22					0 757 25	-	-	-	-	-	
			● 0 758 02 2 m	0 758 29	-	0 758 30	0 758 33	2 x 0 758 35	0 758 07	0 758 12	0 758 17	0 758 22					0 758 25	-	-	-	-	-	
	45 45	50 x 145	0 756 04 2 m	0 756 08	-	0 756 63	① 0 756 66 + ② 0 756 67	2 x 0 756 69	0 756 14	0 756 24	0 756 34	0 756 44				① 0 756 71 + ② 0 756 72	① 0 756 75 + ② 0 756 76	0 756 81 + 0 756 24	0 756 88	0 310 69			
	45 45 45	50 x 180	○ 0 756 06 2 m	0 756 08	-	0 756 61	0 756 66	3 x 0 756 69	0 756 16	0 756 26	0 756 36	0 756 46				0 756 71	0 756 75	0 756 81 + 0 756 26	0 756 88	0 310 69			
			○ 0 110 24 2.5 m	0 756 08	-	0 756 61	0 756 66	3 x 0 756 69	0 756 16	0 756 26	0 756 36	0 756 46				0 756 71	0 756 75	0 756 81 + 0 756 26	0 756 88	0 310 69			
			Antimicrobial ○ 0 757 04 2 m	0 757 29	-	-	0 757 30	3 x 0 757 35	0 757 09	0 757 14	0 757 19	0 757 24				0 757 25	-	-	-	-	-		
			● 0 758 04 2 m	0 758 29	-	0 758 30	0 758 33	3 x 0 758 35	0 758 09	0 758 14	0 758 19	0 758 24				0 758 25	-	-	-	-	-		

1: Partition(s) integral to the body  
2: Internal and external corner angles supplied with multi-compartment partition joint

**Mounting functions**

The Soluclip accessory is very easy to install with any Mosaic or Arteor function and offers the following features:

- Anti-slip
- Anti-pullout
- IP 4X
- Perfect cover finish



- 0 756 90
- 0 757 36 (Antimicrobial)
- 0 757 86
- 0 758 36

**Sockets for flexible cover snap-on trunking**

Sockets for snap-on trunking have been specially designed to meet the requirements for installation and use in total compliance with the new standard EN 50085-2-1. The sockets are fitted with the Soluclip accessory which has the following features:

- Anti-slip
- Anti-pullout
- IP 4X
- Perfect finish

		Standard	Tamperproof	Red	Black
2 x 2P+E		0 772 02	0 772 22	0 772 42	0 772 32
3 x 2P+E		0 772 03	-	0 772 43	0 772 33
Tap-off accessory		0 771 06		-	
2 x RJ 45 Cat. 6 - FTP		0 765 46		0 794 85	
2 x RJ 45 Cat. 5e - FTP		0 765 42		-	
1 x RJ 45 Cat. 6 - UTP		-	-	-	0 794 81
2 x RJ 45 Cat. 6 - STP		-	-	-	0 794 86

