

Desktop multi-outlet extensions



6 535 65



0 546 99



6 535 68

Pack	Cat.Nos	Ready to use multi-outlet extensions
1	6 535 65	Aluminium body Conform to IEC 60-884-1 16 A - 250 VA with shutters Supplied with 3 m cord Composed of: - 4 x 2P+E sockets - 1 x illuminated switch
1	6 535 66	Composed of: - 6 x 2P+E sockets - 1 x illuminated switch
1	6 535 67	Composed of: - 3 x 2P+E sockets - 1 x double USB charger
1	6 535 68	Composed of: - 2 x 2P+E sockets - 2 x 2P+E tamperproof sockets - 2 x RJ 45 Cat.6 UTP 1 module

Empty multi-outlet extensions

1	0 546 90	Aluminium body To be equipped with Arteor or Mosaic Programme wiring accessories 8 modules
1	0 546 91	12 modules
1	0 546 92	16 modules

Fixing accessory for desktop multi-outlet extensions

1	0 546 99	For fixing the desktop multi-outlet extensions on the office furniture
---	----------	--

Cable worm

1	0 535 98	2 compartments Length: 0.75 m White colour Very suitable solution for a safe and design protection of the cabling between desk and floor
---	----------	---

Meeting room multi-outlet extensions with cord



6 535 75



6 535 77

Pack	Cat.Nos	For meeting rooms with central table
1	6 535 74	Equipped with 8 x 2P+E sockets with 45° sloping screw recesses for easy insertion of angled plug On/off switch with light indicator 3680 W at 230 V~ Equipped with 5 m cord (HO5VVF 3G 1.5 mm²) with 2P+E plug Supplied with carrying case High current For connecting up to 8 devices Composition: - 8 x 2P+E with 45° sloping screw recesses
1	6 535 75	With non manageable switch For connecting up to 8 devices and networking up to 6 peripherals (computers...) Requires the use of Ethernet 10/100 base T network cards on the peripherals for 10/100 Mbps data exchanges Composition: - 8 x 2P+E sockets - 1 10/100 base T non manageable switch 6 ports Network cable not supplied
1	6 535 77	With non manageable switch and HD 15 + jack socket For connecting up to 7 devices and networking up to 6 peripherals (computers...) One connection point with HD 15 connector and a 3.5 mm jack Requires the use of Ethernet 10/100 base T network cards on the peripherals for 10/100 Mbps data exchanges Composition: - 7 x 2P+E sockets - 1 10/100 base T non manageable switch with 6 ports - 1 HD 15 socket + 3.5 mm jack - 1 female VGA cord, length 1 m. To be used with a VGA extension - 1 female jack 3.5 mm cord, length 1 m Network cable not supplied