




MYRIUS[®]
NEXTGEN

INSPIRED
BY YOU
CRAFTED
BY US



legrand[®]

LIVE THE ADVANTAGE






with you at **THE HEART**

At Legrand when we dream up something new, guess who drives us to dream bigger? When our engineers do umpteen extra-trials, wonder who do they do it for? When our craftsmen happily work overtime, who secretly motivates them?


Every piece of technology, every byte of data and every stroke of design is created by us, with you at the heart.

The state-of-the-art Myrius NextGen range has been inspired by the lives you lead. Inspired by what the little ones love most or what grandpas and grannies adore. Inspired by what husbands and wives love or sometimes even fight over.

When such inspirations meet Legrand's famed 'Designengineering' philosophy, what you get is the stunning Myrius NextGen range.



**INSPIRED BY
HUES & PATTERNS**



We know just how much India loves its colours and motifs. Crafted by the latest In Mold Decoration (IMD) technology, our CE Certified plates come in myriad colours and unique patterned finishes. With unmatched consistency in quality and the finish of patterns, these modern, sleek and flat designs will add a touch of designer class to any room. So, be it an understated pattern or a bold, colourful look that becomes a showstopper - take your pick from 10 different finishes and live the advantage.









INSPIRED BY YOUR HEALTH-FIRST MANTRA

You prioritize your family's health, hygiene and wellness more than anything else. Inspired, we've created anti-bacterial plates infused with silver ions, which do not let bacteria grow on the surface of switches and plates and accessories throughout its lifespan. One less reason to worry about germs being passed on at home. Live the advantage of a healthy home.



Anti-bacterial
Switch





CHARGING SOLUTIONS







INSPIRED BY YOUR ALWAYS-ON LIFESTYLE

Different users have different requirements. Thankfully our range of Type A and Type C charging solutions ensures that whatever be your type, you'll never run out of charge! And we've been the first to introduce and follow IS standard and the mandatory CRS declaration as per BIS norms. So, live the advantage of so many options





**INSPIRED BY YOUR
CLUTTER-FREE LIFE**




Induction charger*

We all love a life devoid of clutter. A minimal, yet beautiful existence. Just like our induction charger. Forget using messy charging wires for your phone. Simply place it in the induction charger's slot or plug in with USB Port and voila – in no time at all, you have a fully charged phone, without the mess of untangling wires! Live the advantage of a tangle-free life.

*Only charges compatible phones with induction receiver technology





**SMART
CONVENIENCE**





Bluetooth Sound receiver
and Ceiling Speaker

INSPIRED BY THE SECRET PERFORMER IN YOU

Be it crooning alongside your favourite numbers or just jumping up on the bed and dancing to it like no one's watching – we know everyone secretly wants to do these. Our Bluetooth sound receiver and ceiling speaker helps you unlock the performer in you. Thanks to crystal clear audio that turns any room into a concert venue. Live the advantage of enjoying your musical side.





INSPIRED BY YOUR LOVE FOR A GREAT STORY

We know how much you love your page-turners and even a quiet nap in between chapters. Which is why our Modular, Flexible and Dimmable Reading lamp is just perfect. Bright when you are lost in the story and easily dimmed when you want a bit of shuteye. Live the advantage of convenience with an ultra-modern design.



INSPIRED BY YOUR ALWAYS-READY MANTRA OF LIVING

Be prepared – it's one of your favourite philosophies in life, isn't it? We anticipated it. Just as we anticipate any sudden emergency, power cuts or an impromptu adventure into the dark outdoors. Our removable emergency LED lamp is just the right thing you need to show you the way, when all other light fails. Live the advantage of ease.






INSPIRED BY A TOUCH OF YOU

Touch switches in a unique Titane finish. Tested individually for several thousand operations. The promise of long life and low power consumption. High gloss finishing that facilitates easy cleaning. And in-built memory feature for electronic touch switches. When it comes to our touch switches we've kept in mind your needs and touched upon all of them! So, go ahead and live the advantage.





INSPIRED BY YOUR NEED TO STANDOUT

Our Touch Switches bring the ease of convenience and the looks of outstanding design. Modern, sleek, minimal, we are inspired by your global tastes, to make your home as aesthetic as it gets.





Touch Universal LED dimmer




INSPIRED BY YOUR BRIGHT LIFESTYLE

Our Touch Universal Dimmer for all types of dimmable loads, including LED, lets you decide whether you want a dimly lit ambience or a bright as day look





Touch Curtain
Control Switch



INSPIRED BY YOUR MOMENTS BY THE WINDOW

There are moments that you love to draw the curtains apart, sit by the window and look outside as the world passes by. Yet, there are days when you want to shut out the world outside. Our touch curtain control switches are there for you, either way. Live the advantage of privacy or let the world enter through your windows.

INSPIRED BY YOUR LOVE FOR THE HIGHEST STANDARDS

When it comes to certifications, we've left no stone unturned. The best of national and international compliances and certifications have been met in our several products. Legrand is proud to be a part of the prestigious PEP Ecopassport* program, making sustainability quotient top notch. After all we must keep up with your high standards, right? Live the advantage of the very best standards.

*Applicable on selected range of Legrand Products. For more details please connect with our nearest branch representative.





CATALOGUE GUIDE

Switches - Classic White



Switches are ISI marked as per the latest IS 3854:1997
First time in India- Unique Indicator design

Pack	Cat.Nos	Switches 6A 230V AC
20/200	6 792 00	6A Switch 1 way 1M White
20/200	6 792 01	6A Switch 2 way 1M White
20/200	6 792 02	6A Switch 1 way 1M with indicator White
20/200	6 792 03	6A Switch 1 way 1M Light marking White
20/200	6 792 04	6A Switch 1 way 1M with Fan marking White

Pack	Cat.Nos	Switches 10A 230V AC
10/100	6 792 05	10A Switch 1 way 2M White
10/100	6 792 06	10A Switch 2 way 2M White
10/100	6 792 07	10A Intermediate Switch 2M White
10/100	6 792 08	10A Switch 1 way 2M with Indicator White

Pack	Cat.Nos	Switches 16A 230V AC
20/200	6 792 09	16A Switch 1 way 1M White
20/200	6 792 10	16A Switch 2 way 1M White
20/200	6 792 11	16A Switch 1 way 1M with Indicator White

No. of modules

1

1

1

1

1

2

2

2

2

1

1

1

Pack	Cat.Nos	Switches 20A 230V AC
20/200	6 792 12	20A Switch 1 way 1M White
10/100	6 792 13	20A DP Switch 1 way 2M White
10/100	6 792 14	20A DP Switch 1 way 2M with Indicator White
10/100	6 792 15	20A Switch 2 way 2M White

Pack	Cat.Nos	Switches 25A 230V AC
20/200	6 792 16	25A SP 1 way with Indicator 1M White

Pack	Cat.Nos	Switches 32A 230V AC
10/100	6 792 17	32A DP Switch 2M with Indicator White

No. of Modules

1

2

2

2

1

2

Push Buttons



6 792 20



6 792 21



6 792 22



6 792 23



6 792 24

Pack	Cat.Nos	Push Button 6A 230V AC
20/200	6 792 18	6A Push Button SP 1M White
20/200	6 792 19	6A Push Button SP 1 way 1M with Indicator White
20/200	6 792 20	6A Bell Push 1 way 1M White
20/200	6 792 21	6A Bell Push 1 way 1M with Indicator White
10/100	6 792 22	6A Bell Push 1 way 2M White
10/100	6 792 23	6A Bell Push 1 way 2M with Indicator White

Pack	Cat.Nos	Accessories for switches
5/50	6 792 24	Lamp for Switches 230 V AC

No. of Modules

1

1

1

1

2

2

-

Sockets



6 792 25



6 792 26



6 792 27



6 792 28



6 792 32

Pack	Cat.Nos	Sockets 240V AC
		Conforming to IS 1293 : 2019 Shuttered for Child Safety Shutter opens only with phase and neutral insertion simultaneously.
20/200	6 792 25	6/16A 2 Pin Euro-US Socket 1 Module
5/50	6 792 26	16 A 3 Pin Switched Socket 3M
10/100	6 792 27	Multistandard Socket, 2/3 Pin - 6/10/13A 250V AC 2 Pin - 15A for 127V, 2 Module
20/200	6 792 28	6A 5 Pin Universal Socket 2M White
5/50	6 792 29	6/16A Socket 3M White
10/100	6 792 30	6/16A Socket 2M White
10/100	6 792 32	25A Socket 2M White

No. of Modules

1

3

2

2

3

2

2

Dimmers, Fan Regulators, Emergency Light, Skirting Light and Indicators



Pack	Cat.Nos	Dimmers and Fan regulators	No. of modules
		Fan regulators with ISI mark Fan regulators with ease of speed selection Fan regulator models available to suite all Ceiling Fans High capacity sturdy design Light Dimmers	
5/50	6 792 36	Rotary Dimmer 400W 1M White	1
10/100	6 792 37	Rotary Light Dimmer 500W 2M White	2
5/50	6 792 39	Fan Regulator 100W 1M White	1
10/100	6 792 40	Fan Regulator 100W 360 Degree 2M White	2
10/100	6 792 41	Fan Regulator 120W 360 Degree 2M White	2
1/10/100	6 792 42	Fan Regulator 70W 2M White	2
Emergency Light			
		Unique portable torch design with battery backup White Light for better visibility	
1/10/100	6 792 43	Removable LED lamp 2M White	2
Skirting Light			
5/25	6 792 48	Skirting Light with warm White LED 3M White	3
Indicator			
1/10/100	6 792 87	Indicator unit 1M with transparent LED with colored labels White	1

Bell Call Indicator, Buzzer, Infrared Sensors and Remote unit



Pack	Cat.Nos	Bell Call Indicator	No. of Modules
20/200	6 792 49	Bell Call Indicator 1M White	1
Buzzer			
20/200	6 792 50	Buzzer 230V 1M White	1
Infrared sensors			
		High sensitive design with sensitivity and time adjustment Suitable for all type of loads	
1/50	6 792 51	Infrared sensor Switch 400W 2M White	2
Remote unit			
		Sleek, high quality, modular 4 switch remote unit Suitable for all type of loads	
1/5/20	6 792 52	Remote control unit for Light and fan 4M White	4
1/5/30	6 793 03	Remote control hand unit	-

Hospitality function



Hotel Keycard Switch

Pack	Cat.Nos	
1/10	6 792 53	16 A Key card switch Suitable for all type of loads Isolated contacts for switch function
10/100	6 792 55	16A Hotel Key FOB Switch 2M White Credit card size Key FOB

Hotel "DND and MMR" functions

10/100	6 792 56	DND & CMR Indicator 1M + 1M Bell Push White
10/100	6 792 57	DND & CMR (inside) White

Shaver Socket

1/16	6 792 58	Compact design for modular installation Ease for voltage selection Shaver Socket 110/230V AC Monoblock with plate 2M White
1/5/20	6 792 59	Shaver Socket 110/230V AC Monoblock with plate White 4M

No. of Modules
2

2

2

2

2

4

Sockets and Connectors



T.V Sockets

Pack	Cat.Nos		No. of Modules
20/200	6 792 60	T.V co-axial Socket White	1

Data & Voice

20/200	6 792 62	RJ11 Telephone White	1
20/200	6 792 63	Double RJ11 Telephone White	1
20/200	6 792 64	RJ 45 UTP CAT 5 tooless with shutter 1M White	1
20/200	6 792 65	RJ 45 UTP CAT 6 tooless with shutter 1M White	1
10/100	6 792 66	RJ 45 UTP CAT 6 tooless with shutter 2M White	2

Audio-Video Connectors

1/10	6 792 67	Used to transmit high-definition digital/analog audio/video streams between a source (Blu-ray player, computer) and a compatible receiver (TV, LCD video projector...) Preterminated AV connector 1M White	1
------	----------	--	---

Connectors, Sound, Motor starter, Electronic Function



Pack	Cat.Nos	Audio-Video Connectors
1/10	6 792 68	Preterminated projector connector 1M White
1/10	6 792 69	Preterminated HDMI Socket 1M White
1/10/100	6 792 70	Volume Controller 2M
1/10/100	6 792 71	16A Motor starter 2M White
1/10/100	6 792 72	25A Motor starter 2M White
USB chargers (IS13252 (Part 1) / IEC 60950-1)		
1/5/50	6 792 88	Complete family of USB chargers available First time in India - USB C type Charger for fast charging with mandatory CRS marking USB charger 1500 mA 1M type A White
1/10/100	6 792 89	USB charger 3000 mA 2M type A & C White
1/5/50	6 792 90	USB charger 1500 mA 1M type C White

No. of Modules

1

1

2

2

2

1

2

1

Electronic function



Pack	Cat.Nos	Combi (Socket+USB)	
1/5/50	6 792 92	Combi USB tested for optimum operation with high output efficiency Combi twin USB 3100 mA Multistandard Socket type A	3
1/5/50	6 792 93	Combi twin USB 3100 mA Multistandard Socket type A & type C	3
1/5/50	6 792 94	Combi twin USB 3100 mA Multistandard Socket type C	3
Wireless Charger			
1/4	6 792 95	Efficient charging tested as per international standard Modular installation Mobile holder present Available USB for wire charging Induction charger 1A wireless 2.4A USB + dock 2M SUP with mech White 1A charger and one 2.4A USB port to power second device *** charging only with wireless compatible phone having Induction receiver technology.	2
Loud Speakers			
1/6	6 792 98	Compact 6W RMS easy hooking intallation 86db (1W/1M) Sensitivity Ideal for living room, kitchen, Bedroom, offices, canteen Ceiling Loudspeaker 8 Ohms 100mm White	-

Electronic function (contd.)


6 792 99

6 793 04

6 793 09

6 793 10



6 793 06

6 793 05

6 793 15

6 793 16

6 792 75

6 792 76

Pack	Cat.Nos	Sound Diffusion
1/10/100	6 792 99	Bluetooth Technology. Voice messages for easy understanding Compact 2M design with all control functions Inbuilt amplifier, 1.5W X2 with 8 Ohms speaker Ideal for living room, kitchen, Bedroom, offices, canteen Greater than 8 m range Bluetooth sound diffusion 2M



2

Pack	Cat.Nos	Rotary Dimmer Universal
1/10/120	6 793 04	First time in India-High quality universal dimmer for all type of Light loads including LED loads Comes in 1 Module Rotary LED Light dimmer 1M - 50W White



1

Pack	Cat.Nos	Touch Switches
1/50	6 793 08	Range of touch switches Tested for > 40000 switching operations at full load Capacitive touch activation with big touch area for ON THE GO switching Touch Switch 2M 1 way 2 Switch 1000W
1/50	6 793 09	Touch Switch 2M 1 way 1440W
1/50	6 793 10	Touch Switch 2M 2 way 1000W
1/50	6 793 13	Touch Switch 2M 1 way 3000W
1/50	6 793 06	Touch Switch Bell Push 2M 1440W



2

2

2

2

2

2

Pack	Cat.Nos	Touch Regulator, Curtain & Dimmer
1/50	6 793 07	5 step touch Fan regulator Universal scroll type Light dimmer for all type of loads Touch Switch - curtain controller 2M
1/50	6 793 05	Touch Fan Regulator 2M 100W
1/50	6 793 15	300W universal LED touch scroll Dimmer 2M



No. of Modules

2

2

2

Pack	Cat.Nos	Reading Light
1/10	6 793 16	Modular & Flexible handy Light with brightness adjustment Ideal for bedside or table wall installation Warm White light for comfortable reading Reading Light LED 2M White



2

Pack	Cat.Nos	Accessories
20/200	6 792 75	Cable outlet 8mm 1M White
40/400	6 792 76	Blanking plate 1M White
10/100	6 792 77	Blanking plate 2M White



1

1

2

Switches - Charcoal grey



Switches are ISI marked as per the latest IS 3854:1997
First time in India - Unique Indicator design

Pack	Cat.Nos	Switches 6A 230V AC
20/200	6 794 00	6A Switch 1 way 1M Charcoal Grey
20/200	6 794 01	6A Switch 2 way 1M Charcoal Grey
20/200	6 794 02	6A Switch 1 way 1M with Indicator Charcoal Grey
20/200	6 794 03	6A Switch 1 way 1M with Light marking Charcoal Grey
20/200	6 794 04	6A Switch 1 way 1M with Fan marking Charcoal Grey

Pack	Cat.Nos	Switches 10 A 230 V AC
10/100	6 794 05	10A Switch 1 way 2M Charcoal Grey
10/100	6 794 06	10A Switch 2 way 2M Charcoal Grey
10/100	6 794 07	10A intermediate Switch 2M Charcoal Grey
10/100	6 794 08	10A Switch 1 way 2M with Indicator Charcoal Grey

Pack	Cat.Nos	Switches 16A 230V AC
20/200	6 794 09	16A Switch 1 way 1M Charcoal Grey
20/200	6 794 10	16A Switch 2 way 1M Charcoal Grey
20/200	6 794 11	16A Switch 1 way 1M with Indicator Charcoal Grey

No. of Modules	Cat.Nos	Switches 20A 230V AC	No. of Modules
1	20/200	6 794 12	1
1	10/100	6 794 13	2
1	10/100	6 794 14	2
1	10/100	6 794 15	2
1	20/200	6 794 16	1
2	10/100	6 794 17	2

Push buttons



Pack	Cat.Nos	Push Button 6A 230V AC
20/200	6 794 18	6A Push Button SP 1 way 1M Charcoal Grey
20/200	6 794 19	6A Push Button 1 way 1M Indicator Charcoal Grey
20/200	6 794 20	6A Bell Push 1 way 1M Charcoal Grey
20/200	6 794 21	6A Bell Push 1 way 1M with Indicator Charcoal Grey
10/100	6 794 22	6A Bell Push 1 way 2M Charcoal Grey
10/100	6 794 23	6A Bell Push 1 way 2M with Indicator Charcoal Grey

No. of Modules
1

1


1

1

2

2

Sockets



Pack	Cat.Nos	Sockets 240V AC	No. of Modules
		Conforming to IS 1293 : 2019 Shuttered for Child Safety Shutter opens only with phase and neutral insertion simultaneously	
20/200	6 794 24	6/16 A 2 pin Euro US Socket 1M Charcoal Grey	1
5/50	6 794 26	16 A 3 pin Switched Socket 3M Charcoal Grey	3
10/100	6 794 25	Multistandard Socket, 2/3 Pin - 6/10/13A 250V AC 2 Pin -15A for 127V, 2 Module Charcoal Grey	2
20/200	6 794 28	6A 5 Pin Universal Socket 2M Charcoal Grey	2
5/50	6 794 29	6/16A Socket 3M Charcoal Grey	3
10/100	6 794 30	6/16A Socket 2M Charcoal Grey	2
10/100	6 794 32	25 A Socket 2M Charcoal Grey	2

Fan regulator and dimmer



6 794 36 6 794 37 6 794 39

Pack	Cat.Nos	Dimmers and Fan Regulators	
		Fan regulators with ISI mark Fan regulators with ease of speed selection Fan regulator models available to suite almost all Ceiling Fans High capacity sturdy design Light dimmers	
5/50	6 794 36		Rotary Dimmer 400W 1M Charcoal Grey
10/100	6 794 37		Rotary Light Dimmer 500W 2M Charcoal Grey
5/50	6 794 39		Fan Regulator 100W 1M Charcoal Grey
10/100	6 794 40		Fan Regulator 100W 360 Degree 2M Charcoal Grey
10/100	6 794 41		Fan Regulator 120W 360 Degree 2M Charcoal Grey
1/10/100	6 794 42		Fan Regulator 70W 2M Charcoal Grey
Skirting Light			
5/25	6 794 48		Skirting Light with Warm White LED 3M Charcoal Grey

No. of Modules

1
2
1
2
2
2

3

Skirting light, bell call indicators, buzzer, remote unit



6 794 49 6 794 50 6 794 52 6 793 03

Pack	Cat.Nos	Bell Call Indicator		No. of Modules
20/200	6 794 49		Bell Call indicator Charcoal Grey 1M	1
20/200	6 794 50		Buzzer 230V 1M Charcoal Grey	1
Remote Unit				
1/5/20	6 794 52		Sleek, high quality, modular 4 switch Remote unit suitable for all type of loads Remote control unit for Light and Fan 4M Charcoal Grey	4
1/5/30	6 793 03		Remote control hand unit	-

Hospitality functions



6 794 53



6 794 54



6 794 55



6 794 59

Pack	Cat.Nos	Hospitality Function
1/10	6 794 53	Hotel Keycard Switch 16A Key card switch Suitable for all type of loads Isolated contacts for Switch function
10/100	6 792 55	16A Hotel Key FOB SW Charcoal Grey Credit card size Key FOB
10/100	6 794 54	DND & CMR Indicator 1M + 1M Bell Push Charcoal Grey
10/100	6 794 55	DND & CMR (inside) Charcoal Grey
1/16	6 794 58	Shaver Socket 120/240V AC Monoblock with plate 2M Charcoal Grey
1/5/20	6 794 59	Shaver Socket 120/230V AC Monoblock with plate 4M Charcoal Grey

No. of Modules
2

-

2

2

2

4

Sockets and connectors



6 794 60



6 794 62



6 794 64



6 794 67



6 794 70

Pack	Cat.Nos	TV Sockets	No. of Modules
20/200	6 794 60	T.V co-axial Socket Charcoal Grey	1
20/200	6 794 62	RJ11 Telephone Charcoal Grey	1
20/200	6 794 63	Double RJ11 Telephone Charcoal Grey	1
20/200	6 794 64	RJ 45 UTP CAT 5 tooless with shutter 1M Charcoal Grey	1
20/200	6 794 65	RJ 45 UTP CAT 6 tooless with shutter 1M Charcoal Grey	1
10/100	6 794 66	RJ 45 UTP CAT 6 tooless with shutter 2M Charcoal Grey	2
1/10	6 794 67	Preterminated AV connector 1M Charcoal Grey	1
1/10	6 794 68	Preterminated HDMI Socket 1M Charcoal Grey	1
1/10	6 794 69	Preterminated projector connector 1M Charcoal Grey	1
1/10/100	6 794 70	Volume Controller 2M Charcoal Grey	2

Data & Voice

Audio Video sockets

Used to transmit high-definition digital/analog
Audio/Video streams between a source
(Blu-ray player, computer) and a compatible receiver
(T.V, LCD video projector...)

Electronic function



6 794 71



6 794 89



6 794 92



6 794 97



6 794 98



6 794 75



6 794 76

Pack	Cat.Nos	Motor Starter		No. of Modules
1/10/100	6 794 71		16A Motor Starter 2M Charcoal Grey	
1/10/100	6 794 72		25A Motor Starter 2M Charcoal Grey	2
USB Chargers (IS13252 (Part 1) / IEC 60950-1)				
Complete family of USB chargers available First time in India - USB C type Charger for fast charging with mandatory CRS marking				
1/5/100	6 794 88		USB charger 1500 mA 1M type A Charcoal Grey	1
1/10/100	6 794 89		USB charger 3000 mA 2M type A & C Charcoal Grey	2
1/5/100	6 794 90		USB charger 1500 mA 1M type C Charcoal Grey	1
Combi (Socket+USB)				
Combi USB tested for optimum operation with high output efficiency				
1/5/50	6 794 92		Combi twin USB 3100 mA multistandard Socket type A Charcoal Grey	3
1/5/50	6 794 93		Combi twin USB 3100 mA multistandard Socket type A & type C Charcoal Grey	3
1/5/50	6 794 94		Combi twin USB 3100 mA multistandard Socket type C Charcoal Grey	3

Pack	Cat.Nos	Sound Diffusion		
		Bluetooth Technology. Voice messages for easy understanding Compact 2M design with all control functions Inbuilt amplifier, 1.5W X2 with 8 Ohms speaker Ideal for living room, kitchen, Bedroom, offices, canteen Greater than 8m range		
1/10/100	6 794 97		Bluetooth sound diffusion 2M Charcoal Grey	No. of Modules 2
Rotary Dimmer Universal				
First time in India-High quality universal dimmer for all type of light loads including LED loads Comes in 1 module				
1/10/120	6 794 98		Rotary LED Light Dimmer 50W 1M Charcoal Grey	1
Accessories				
20/200	6 794 75		Cable outlet 8mm 1M Charcoal Grey	1
40/400	6 794 76		Blanking plate 1M Charcoal Grey	1

Switches - Classic white (Antibacterial Range)



Switches are ISI marked as per the latest IS 3854:1997
 First time in India- Unique Signature design.
 With Anti-Bacterial properties

Pack	Cat.Nos	Switches 6A 230V AC	
20/200	6 793 20		6A SW 1 way 1M White Anti-Bacterial
20/200	6 793 21		6A SW 2 way 1M White Anti-Bacterial
20/200	6 793 24		6A Bell Push 1M White Anti-Bacterial
Switches 16A 230V AC			
20/200	6 793 22		16A SW 1 way 1M White Anti-Bacterial
20/200	6 793 23		16A SW 2 way 1M White Anti-Bacterial
Sockets 240V AC			
Conforming to IS 1293 : 2019 Shuttered for Child Safety Shutter opens only with phase and neutral insertion simultaneously.			
10/100	6 793 26		Multistandard Socket, 2/3 Pin - 6/10/13A 250V AC 2 Pin -15A for 127V, 2M
20/200	6 793 27		6A 5 Pin Universal Socket 2M
10/100	6 793 28		6/16A Socket 2M
5/50	6 793 29		6/16A Socket 3M

No. of Modules

1

1

1

1

1

2

2

2

3

Fan Regulators

Fan Regulators with ISI mark
 Fan Regulators with ease of speed selection
 Fan Regulator models available to suite almost all Ceiling Fans

10/100 6 793 25 Fan Regulator 120W 360 Degree 2M

No. of Modules

2

TV sockets

20/200 6 793 30 TV. Socket 1M Anti-Bacterial

1

Data & Voice

20/200 6 793 31 RJ 11 Telephone Socket 1M Anti-Bacterial

1

20/200 6 793 32 RJ 45 CAT 6 UTP Anti-Bacterial 1M

1

Accessories

40/400 6 793 33 Blanking plate 1M White Anti-Bacterial

1

Plates with frame



6 795 02

6 795 04



6 795 06

6 795 08

Pack	Cat.Nos	Plate Frame White	No. of Modules	Dimension (mm)
20/200	6 795 01	Plate+frame 1M White	1	86 x 86
20/200	6 795 02	Plate+frame 2M White	2	86 x 86
10/100	6 795 03	Plate+frame 3M White	3	86 x 121
10/100	6 795 04	Plate+frame 4M White	4	86 x 146
5/50	6 795 06	Plate+frame 6M White	6	86 x 224
5/50	6 795 08	Plate+frame 8M White	8	86 x 245
5/25	6 795 09	Plate+frame 2x4M White	2x4	172 x 146
5/50	6 795 10	Plate+frame 9M White	9	288 X 86
10	6 795 12	Plate+frame 12M White	12	172 x 224
10	6 795 16	Plate+frame 16M White	16	172 x 224
10	6 795 18	Plate+frame 18M White	18	240 x 224



6 795 22

6 795 23



6 795 24

6 795 28

Pack	Cat.Nos	Plate Frame Ice White	No. of Modules	Dimension (mm)
1/5/30	6 795 21	Plate+frame 1M Ice White	1	86 x 86
1/5/30	6 795 22	Plate+frame 2M Ice White	2	86 x 86
1/20	6 795 23	Plate+frame 3M Ice White	3	86 x 121
1/20	6 795 24	Plate+frame 4M Ice White	4	86 x 146
1/10	6 795 26	Plate+frame 6M Ice White	6	86 x 224
1/10	6 795 28	Plate+frame 8M Ice White	8	86 x 245
1/5	6 795 29	Plate+frame 2x4M Ice White	2x4	172 x 146
1/5	6 795 32	Plate+frame 12M Ice White	12	172 x 224
1/5	6 795 36	Plate+frame 16M Ice White	16	172 x 224
1/5	6 795 38	Plate+frame 18M Ice White	18	240 x 224

Plates with frame



6 795 42

6 795 44



6 775 46

6 795 48

Pack	Cat.Nos	Plate Frame Ice Black			No. of Modules	Dimension (mm)
1/5/30	6 795 41		Plate+frame 1M Ice Black		1	86 x 86
1/5/30	6 795 42		Plate+frame 2M Ice Black		2	86 x 86
1/20	6 795 43		Plate+frame 3M Ice Black		3	86 x 121
1/20	6 795 44		Plate+frame 4M Ice Black		4	86 x 146
1/10	6 795 46		Plate+frame 6M Ice Black		6	86 x 224
1/10	6 795 48		Plate+frame 8M Ice Black		8	86 x 245
1/5	6 795 49		Plate+frame 2x4M Ice Black		2x4	172 x 146
1/5	6 795 52		Plate+frame 12M Ice Black		12	172 x 224
1/5	6 795 56		Plate+frame 16M Ice Black		16	172 x 224
1/5	6 795 58		Plate+frame 18M Ice Black		18	240 x 224



6 795 62

6 795 64



6 795 66

6 795 68

Pack	Cat.Nos	Plate Frame Pearl Champagne			No. of Modules	Dimension (mm)
1/5/30	6 795 61		Plate+frame 1M Pearl Champagne		1	86 x 86
1/5/30	6 795 62		Plate+frame 2M Pearl Champagne		2	86 x 86
1/20	6 795 63		Plate+frame 3M Pearl Champagne		3	86 x 121
1/20	6 795 64		Plate+frame 4M Pearl Champagne		4	86 x 146
1/10	6 795 66		Plate+frame 6M Pearl Champagne		6	86 x 224
1/10	6 795 68		Plate+frame 8M Pearl Champagne		8	86 x 245
1/5	6 795 69		Plate+frame 2x4M Pearl Champagne		2x4	172 x 146
1/5	6 795 72		Plate+frame 12M Pearl Champagne		12	172 x 224
1/5	6 795 76		Plate+frame 16M Pearl Champagne		16	172 x 224
1/5	6 795 78		Plate+frame 18M Pearl Champagne		18	240 x 224

Plates with Frame



6 795 82



6 795 84



6 795 86



6 795 88



6 796 02



6 796 04



6 796 06



6 796 08

Pack	Cat.Nos	Plate Frame Sonic Silver		No. of Modules	Dimension (mm)
1/5/30	6 795 81		Plate+frame 1M Sonic Silver	1	86 x 86
1/5/30	6 795 82		Plate+frame 2M Sonic Silver	2	86 x 86
1/20	6 795 83		Plate+frame 3M Sonic Silver	3	86 x 121
1/20	6 795 84		Plate+frame 4M Sonic Silver	4	86 x 146
1/10	6 795 86		Plate+frame 6M Sonic Silver	6	86 x 224
1/10	6 795 88		Plate+frame 8M Sonic Silver	8	86 x 245
1/5	6 795 89		Plate+frame 2x4M Sonic Silver	2x4	172 x 146
1/5	6 795 92		Plate+frame 12M Sonic Silver	12	172 x 224
1/5	6 795 96		Plate+frame 16M Sonic Silver	16	172 x 224
1/5	6 795 98		Plate+frame 18M Sonic Silver	18	240 x 224


Pack	Cat.Nos	Plate Frame Dark Fade		No. of Modules	Dimension (mm)
1/5/30	6 796 01		Plate+frame 1M Dark Fade	1	86 x 86
1/5/30	6 796 02		Plate+frame 2M Dark Fade	2	86 x 86
1/20	6 796 03		Plate+frame 3M Dark Fade	3	86 x 121
1/20	6 796 04		Plate+frame 4M Dark Fade	4	86 x 146
1/10	6 796 06		Plate+frame 6M Dark Fade	6	86 x 224
1/10	6 796 08		Plate+frame 8M Dark Fade	8	86 x 245
1/5	6 796 09		Plate+frame 2x4M Dark Fade	2x4	172 x 146
1/5	6 796 12		Plate+frame 12M Dark Fade	12	172 x 224
1/5	6 796 16		Plate+frame 16M Dark Fade	16	172 x 224
1/5	6 796 18		Plate+frame 18M Dark Fade	18	240 x 224

Plates with frame



6 796 22

6 796 24




6 796 26

6 796 28



6 796 42

6 796 44



6 796 46

6 796 48

Pack	Cat.Nos	Plate Frame Interlude		
1/5/30	6 796 21		Plate+frame 1M Interlude	No. of Modules 1
1/5/30	6 796 22		Plate+frame 2M Interlude	2
1/20	6 796 23		Plate+frame 3M Interlude	3
1/20	6 796 24		Plate+frame 4M Interlude	4
1/10	6 796 26		Plate+frame 6M Interlude	6
1/10	6 796 28		Plate+frame 8M Interlude	8
1/5	6 796 29		Plate+frame 2x4M Interlude	2x4
1/5	6 796 32		Plate+frame 12M Interlude	12
1/5	6 796 36		Plate+frame 16M Interlude	16
1/5	6 796 38		Plate+frame 18M Interlude	18
				Dimension (mm)
				86 x 86
				86 x 86
				86 x 121
				86 x 146
				86 x 224
				86 x 245
				172 x 146
				172 x 224
				172 x 224
				240 x 224

Pack	Cat.Nos	Plate Frame Trinity		
1/5/30	6 796 41		Plate+frame 1M Trinity	No. of Modules 1
1/5/30	6 796 42		Plate+frame 2M Trinity	2
1/20	6 796 43		Plate+frame 3M Trinity	3
1/20	6 796 44		Plate+frame 4M Trinity	4
1/10	6 796 46		Plate+frame 6M Trinity	6
1/10	6 796 48		Plate+frame 8M Trinity	8
1/5	6 796 49		Plate+frame 2x4M Trinity	2x4
1/5	6 796 52		Plate+frame 12M Trinity	12
1/5	6 796 56		Plate+frame 16M Trinity	16
1/5	6 796 58		Plate+frame 18M Trinity	18
				Dimension (mm)
				86 x 86
				86 x 86
				86 x 121
				86 x 146
				86 x 224
				86 x 245
				172 x 146
				172 x 224
				172 x 224
				240 x 224

Plates with frame



6 796 62



6 796 64



6 796 66



6 796 68



6 796 82



6 796 84



6 796 86



6 796 88

Pack	Cat.Nos	Plate Frame Luminar		No. of Modules	Dimension (mm)
1/5/30	6 796 61		Plate+frame 1M Luminar	1	86 x 86
1/5/30	6 796 62		Plate+frame 2M Luminar	2	86 x 86
1/20	6 796 63		Plate+frame 3M Luminar	3	86 x 121
1/20	6 796 64		Plate+frame 4M Luminar	4	86 x 146
1/10	6 796 66		Plate+frame 6M Luminar	6	86 x 224
1/10	6 796 68		Plate+frame 8M Luminar	8	86 x 245
1/5	6 796 69		Plate+frame 2x4M Luminar	2x4	172 x 146
1/5	6 796 72		Plate+frame 12M Luminar	12	172 x 224
1/5	6 796 76		Plate+frame 16M Luminar	16	172 x 224
1/5	6 796 78		Plate+frame 18M Luminar	18	240 x 224

Pack	Cat.Nos	Plate Frame Stellar		No. of Modules	Dimension (mm)
1/5/30	6 796 81		Plate+frame 1M Stellar	1	86 x 86
1/5/30	6 796 82		Plate+frame 2M Stellar	2	86 x 86
1/20	6 796 83		Plate+frame 3M Stellar	3	86 x 121
1/20	6 796 84		Plate+frame 4M Stellar	4	86 x 146
1/10	6 796 86		Plate+frame 6M Stellar	6	86 x 224
1/10	6 796 88		Plate+frame 8M Stellar	8	86 x 245
1/5	6 796 89		Plate+frame 2x4M Stellar	2x4	172 x 146
1/5	6 796 92		Plate+frame 12M Stellar	12	172 x 224
1/5	6 796 96		Plate+frame 16M Stellar	16	172 x 224
1/5	6 796 98		Plate+frame 18M Stellar	18	240 x 224

Plates with frame (antibacterial range)



6 793 42



6 793 44



6 793 46



6 793 48

Pack	Cat.Nos	Plate Frame Anti-Bacterial			No. of Modules	Dimension (mm)
20/200	6 793 41		Plate+frame 1M Anti-Bacterial		1	86 x 86
20/200	6 793 42		Plate+frame 2M Anti-Bacterial		2	86 x 86
10/100	6 793 43		Plate+frame 3M Anti-Bacterial		3	86 x 121
10/100	6 793 44		Plate+frame 4M Anti-Bacterial		4	86 x 146
5/50	6 793 46		Plate+frame 6M Anti-Bacterial		6	86 x 224
5/50	6 793 48		Plate+frame 8M Anti-Bacterial		8	86 x 245
5/25	6 793 49		Plate+frame 2x4M Anti-Bacterial		2x4	172 x 146
5/50	6 793 50		Plate+frame 9M Anti-Bacterial		9	288 X 86
10	6 793 52		Plate+frame 12M Anti-Bacterial		12	172 x 224
10	6 793 56		Plate+frame 16M Anti-Bacterial		16	172 x 224
10	6 793 58		Plate+frame 18M Anti-Bacterial		18	240 x 224

Mounting Boxes



Pack	Cat.Nos	Metal Flush Boxes	
40	6 890 07		Flush Box - 1/2 Module
40	6 890 08		Flush Box - 3 Module
40	6 890 09		Flush Box - 4 Module
40	6 890 10		Flush Box - 6 Module
40	6 890 42		Flush Box - 8 Module
20	6 890 31		Flush Box - 8 Module (2 row x 4)
10	6 890 11		Flush Box - 12/16 (2 row x 6) Module
10	6 890 12		Flush Box - 18 Module

No. of Modules

1/2

3

4

6

8

8

12/16

18

Plastic and metal surface boxes



Pack	Cat.Nos	Plastic Surface Boxes	
10/50	6 733 02		Surface Box - 1/2 Module
5/35	6 733 03		Surface Box - 3 Module
5/25	6 733 04		Surface Box - 4 Module
1/10	6 733 06		Surface Box - 6 Module
1/5	6 733 08		Surface Box - 8 Module
1/5	6 733 05	Surface Box - 8 (2 row x 4) Module	
Metal Surface Boxes			
1/6	6 890 21		Surface Box - 12/16 (2 row x 6) Module
1/4	6 890 22		Surface Box - 18 Module

No. of Modules

1/2

3

4

6

8

8

12/16

18

6 A touch switch 1 - way

Technical data

6A touch switch 2M-1W


Cat.No 6 793 09

Characteristics


	-5 °C ... +45 °C	-1 °C ... +70 °C	≤ 40 mm	100 - 240 V~ 50 / 60 Hz	1...4 mm²

	1	2	3	4	5	6	7
240V~	1440W	1000V AC	1000V AC	250W	250W	250W	4A(PF≥0.6)
100V~	600W	400V AC	400V AC	100W	100W	100W	


Operation



Wiring



Fixing



Safety instructions

When use this product, please install a fuse or protective device to protect the product in the line of COM input, the protective device should be equal to 6 A / 100-240 V.
This product should be installed preferably by a qualified electrician. Incorrect installation and use can entail risk of electric shock or fire. Before carrying out the installation, read the instructions and take account of the product's specific mounting location. Do not open up the device. All Legrand products must be exclusively opened and repaired by personnel trained and approved by LEGRAND. Any unauthorized opening or repair completely cancels all liabilities and the rights to replacement and guarantees. Only use genuine accessories.

Electronic switch 6A touch 2M 1W-2-SW control

Technical data

Electronic switch 6A touch 2M-1W-2-SW control


Cat.No 6 793 08

Characteristics


	0 °C/+45 °C	-10 °C/+70 °C	40 mm	100-240 V~ 50/60 Hz	1~4 mm²

	①	②	③	④	⑤	⑥	⑦
240 V ~	1000W	700 VAC	700 VAC	250W	250W	250W	4 A(FP=0.6)
100 V ~	400W	300 VAC	300 VAC	100W	100W	100W	


Operation



Wiring



Fixing



Safety instructions


When use this product, please install a fuse or protective device to protect the product in the line of COM input, the protective device should be equal to 6 A / 100-240 V.
This product should be installed preferably by a qualified electrician. Incorrect installation and use can entail risk of electric shock or fire. Before carrying out the installation, read the instructions and take account of the product's specific mounting location. Do not open up the device. All Legrand products must be exclusively opened and repaired by personnel trained and approved by LEGRAND. Any unauthorized opening or repair completely cancels all liabilities and the rights to replacement and guarantees. Only use genuine accessories.

■ Technical data

6A touch switch 2M-2W

Cat.No 6 793 10


Characteristics




			100 - 240 V~ 50 / 60 Hz	
-5 °C/+45 °C	-10 °C/+70 °C	≤ 40 mm		1...4 mm ²

	1	2	3	4	5	6	7
240V~	1000W	700V AC	700V AC	250W	250W	250W	4A(PF≥0.6)
100V~	400W	300V AC	300V AC	100W	100W	100W	

Operation




Wiring



6 A touch switch 2 - way (contd.)

Fixing



Safety instructions

When use this product, please install a fuse or protective device to protect the product in the line of COM input, the protective device should be equal to 6 A / 100~240 V.

This product should be installed preferably by a qualified electrician. Incorrect installation and use can entail risk of electric shock or fire.

Before carrying out the installation, read the instructions and take account of the product's specific mounting location.

Do not open up the device. All Legrand products must be exclusively opened and repaired by personnel trained and approved by LEGRAND.

Any unauthorized opening or repair completely cancels all liabilities and the rights to replacement and guarantees.

Only use genuine accessories.


16 A touch switch 2W- 1W

Technical data

16A touch switch 2M-1W

Cat.No 6 793 13

Characteristics



-5 °C.../+45 °C

-10 °C.../+70 °C


≤ 40 mm

100 - 240 V~
50 / 60 Hz


1...4 mm²

	1	2	3	4	5	6	7
240V~	3000W	2000V AC	2000V AC	600W	600W	500W	8A(PF≥0.6)
100V~	1250W	800V AC	800V AC	250W	250W	300W	


Operation



Wiring



Fixing



Safety instructions

When use this product, please install a fuse or protective device to protect the product in the line of COM input, the protective device should be equal to 6 A / 100~240 V.

This product should be installed preferably by a qualified electrician. Incorrect installation and use can entail risk of electric shock or fire. Before carrying out the installation, read the instructions and take account of the product's specific mounting location. Do not open up the device. All Legrand products must be exclusively opened and repaired by personnel trained and approved by LEGRAND. Any unauthorized opening or repair completely cancels all liabilities and the rights to replacement and guarantees. Only use genuine accessories.

6 A touch switch Bell Push 2M

300 W universal LED touch dimmer 2M

Technical data

6A touch switch Bell Push 2M

Cat.No 6 793 06


Characteristics

	-5 °C/+45 °C	-10 °C/+70 °C	≤ 40 mm	100 - 240 V~ 50 / 60 Hz	1...4 mm ²


	1	2	3	4
240V~	1440W	200W	200W	200W
100V~	600W	100W	100W	100W

- 1 Incandescent lamp
- 2 Electronic triggered with tunes
- 3 Electric magnetic long bell (ding dong)
- 4 Electric Buzzer-Vibrating


Wiring



Operation



Fixing



! Safety instructions

When use this product, please install a fuse or protective device to protect the product in the line of COM input, the protective device should be equal to 6 A / 100~240 V.

This product should be installed preferably by a qualified electrician. Incorrect installation and use can entail risk of electric shock or fire. Before carrying out the installation, read the instructions and take account of the product's specific mounting location. Do not open up the device. All Legrand products must be exclusively opened and repaired by personnel trained and approved by LEGRAND. Any unauthorized opening or repair completely cancels all liabilities and the rights to replacement and guarantees. Only use genuine accessories.

Technical data

300W universal LED touch dimmer 2M


Cat.No 6 793 15

Characteristics

	-5 °C.../+45 °C	-10 °C.../+70 °C	≤ 40 mm	100 - 240 V~ 50 / 60 Hz	1...4 mm ²

	R	L	C/L		
			Dimmable		
240V~ 50Hz	5...300W	5... 300V AC	5... 300V AC	5... 300V AC	5...75W ≤ 10 x
100V~ 60Hz	5...150W	5... 150V AC	5... 150V AC	5... 150V AC	5...37W ≤ 10 x

Local dimming:




Technical data



300 W Universal LED touch dimmer - 2M

Cat.No 6 793 15


Characteristics




Local+remote/auxiliary dimming:




Min. brightness settings




CFL setting




Load type setting



Factory reset



Fixing



Safety instructions


This product should be installed preferably by a qualified electrician. Incorrect installation and use can entail risk of electric shock or fire. Before carrying out the installation, read the instructions and take account of the product's specific mounting location. Do not open up the device. All Legrand products must be exclusively opened and repaired by personnel trained and approved by LEGRAND. Any unauthorized opening or repair completely cancels all liabilities and the rights to replacement and guarantees. Only use genuine accessories.

Technical data



Touch Fan regulator 2M-100W

Cat.No 6 793 05

Characteristics



①	
240~50HZ	100W



Safety instructions


This product should be installed preferably by a qualified electrician. Incorrect installation and use can entail risk of electric shock or fire. Before carrying out the installation, read the instructions and take account of the product's specific mounting location. Do not open up the device. All Legrand products must be exclusively opened and repaired by personnel trained and approved by LEGRAND. Any unauthorized opening or repair completely cancels all liabilities and the rights to replacement and guarantees. Only use genuine accessories.

Technical data

Electronic switch touch- curtain controller 2M


Cat.No 6 793 07

Characteristics




①	
240 V~	200V AC
100 V~	100 V AC


Operation



Wiring



Fixing




Safety instructions

When use this product, please install a fuse or protective device to protect the product in the line of COM input, the protective device should be equal to 6 A / 100~240 V.
This product should be installed preferably by a qualified electrician. Incorrect installation and use can entail risk of electric shock or fire. Before carrying out the installation, read the instructions and take account of the product's specific mounting location. Do not open up the device. All Legrand products must be exclusively opened and repaired by personnel trained and approved by LEGRAND. Any unauthorized opening or repair completely cancels all liabilities and the rights to replacement and guarantees. Only use genuine accessories.

Technical data

Bluetooth Sound Receiver

Cat.Nos 6 792 99 / 6 794 97




Utilization


			Bluetooth (A2DP)		Works with Bluetooth technology devices
100-240V AC	STEREO 2X1.5 W	4 mA Max AC	> 8 m	40° 0° +5 °C +45 °C	
	1 WX2/16 Ω 1.5 WX2/8 Ω 2 WX2/4 Ω				

Bluetooth device Name - "legrand"

Wiring




Function




Note :Long press (for 2S)

Technical data

Bluetooth Connection



Mounting



Safety instructions

GB 1E

This product should be installed in line with installation rules, preferably by a qualified electrician. Incorrect installation and use can lead to risk of electric shock or fire. Before carrying out the installation, read the instructions and take account of the product's specific mounting location.


Do not open up, dismantle, alter or modify the device except where specifically required to do so by the instructions. All Legrand products must be opened and repaired exclusively by personnel trained and approved by LEGRAND. Any unauthorized opening or repair completely cancels all liabilities and the rights to replacement and guarantees.

Use only Legrand brand accessories.

Technical data

Remote for Fan and Light mechanism

Cat.Nos 6 794 52 / 6 792 52




 240 V AC 50 Hz	 ①	 ②	 ③	 ④	 ⑤	 ⑥
Max.	1x2.5 mm²	400V AC	200V AC	200V AC	150V AC	100V AC
				Q26 Q38		

Utilization


- Incandescent bulbs
- Halogen lamp 230V~
- Low voltage halogen lamps
- Fluorescent tube light
- Ceiling Fan (OFF + 4 Variable speed steps)
- LED Lamps (Max 3 Units)

Description


Infrared receiver and controller unit




Infrared remote transmitter



Wiring diagram



Replacement of old battery



Safety instructions


This product should be installed in line with installation rules, preferably by a qualified electrician. Incorrect installation and use can lead to risk of electric shock or fire. Before carrying out the installation, read the instructions and take account of the product's specific mounting location. Do not open up, dismantle, alter or modify the device except where specifically required to do so by the instructions. All Legrand products must be opened and repaired exclusively by personnel trained and approved by LEGRAND. Any unauthorised opening or repair completely cancels all liabilities and the rights to replacement and guarantees. Use only Legrand brand accessories.

Technical data

Rotary LED dimmer 1M

Cat.Nos 6 793 04 / 6 794 98


Characteristics




0° C ... + 45° C	- 10° C ... + 70° C	≤ 40 mm	100 - 240 V~ 50 / 60 Hz	1 x 2.5 mm²	

240 V	Max.	200W	200W	200V AC	200V AC	200V AC	200V AC	50W or 8 lamps max.
	Min.	3W	3W	3V AC	3V AC	3V AC	3V AC	3W
100 V	Max.	100W	100W	100V AC	100V AC	100V AC	100V AC	37W or 8 lamps max.
	Min.	3W	3W	3V AC	3V AC	3V AC	3V AC	3W

Operation




Wiring



Safety instructions

This product should be installed preferably by a qualified electrician. Incorrect installation and use can entail risk of electric shock or fire. Before carrying out the installation, read the instructions and take account of the product's specific mounting location. Do not open up the device. All Legrand products must be exclusively opened and repaired by personnel trained and approved by LEGRAND. Any unauthorized opening or repair completely cancels all liabilities and the rights to replacement and guarantees. Only use genuine accessories.





Fixing




Technical data

Wireless induction charger

Cat.No 6 792 95




Wireless charging only with compatible mobile phones having induction receiver technology.



Technical data

Wireless charger (contd.)

Cat.No 6 792 95



⚠ Safety instructions


This product should be installed in compliance with installation rules, preferably by a qualified electrician. Incorrect installation and/or incorrect use can lead to risk of electric shock or fire. Before carrying out the installation, read the instructions and take account of the product's specific mounting location.
Do not open up, dismantle, alter or modify the device except where specifically required to do so by the instructions. All Legrand products must be opened and repaired exclusively by personnel trained and approved by Legrand. Any unauthorised opening or repair completely cancels all liabilities and the rights to replacement and guarantees. Use only Legrand brand accessories.

Technical data

Infrared sensor switch




Cat.No 6 792 51

Characteristics





			100 - 240 V~ 50 / 60 Hz	
-5 °C/+45 °C	-10 °C/+70 °C	40 mm		1-4 mm²
PIR	day/dusk/night	30S/90S/180S	40 m²	

	①	②	③	④	⑤	⑥	⑦
230 V~	400W	200V AC	200V AC	200V AC	200V AC	100V AC	100V AC
110 V~	200W	100V AC	100V AC	100V AC	100V AC	50V AC	50V AC
	1.7 A	0.85 A	0.85 A	0.85A	0.85A	0.42A	0.42A




Wiring



day: 20~500lux
dusk: 3~20lux
night: <3lux


180S
90S
30S

Working



* A delay of 1min to be observed after power ON for functioning of the switch.

Fixing



⚠ Safety instructions


This product should be installed preferably by a qualified electrician. Incorrect installation and use can entail risk of electric shock or fire. Before carrying out the installation, read the instructions and take account of the product's specific mounting location. Do not open up the device. All Legrand products must be exclusively opened and repaired by personnel trained and approved by LEGRAND. Any unauthorized opening or repair completely cancels all liabilities and the rights to replacement and guarantees. Only use genuine accessories.

■ Technical data

16A Hotel Key FOB switch

Cat.Nos 6 792 53

Characteristics



	16A max
	16 A / 230 V~μ cosφ = 1
	4 A / 230 V~μ cosφ = 0.6


Utilization

	①	②	③	④	⑤
	40° 0° 230 V~ 50 Hz	Light bulb	Fluorescent lamp	Fluorescent lamp	LED lamp
Max.		1800W	800W	400V AC	800V AC
				100V AC	


1. 1800 W lamp incandescent or halogen with ferromagnetic transformer.
2. 800 W inductive (motor).
3. 400 VA compensated fluorescent lamp.
4. 800 VA fluorescent lamp with electronic ballast.
5. 100 VA LED lamp.

Important: For load higher than indicated in the above table, use a contactor.

Installation




Wiring




Shaver Socket


Fixing



Use



Dismantling / Maintenance



Safety instructions

This product should be installed in compliance with installation rules, preferably by a qualified electrician. Incorrect installation and use can lead to risk of electric shock or fire. Before carrying out the installation, read the instructions and take account of the product's specific mounting location.

Do not open up, dismantle, alter or modify the device except where specifically required to do so by the instructions. All Legrand products must be opened and repaired exclusively by personnel trained and approved by Legrand. Any unauthorised opening or repair completely cancels all liabilities and the rights to replacement and guarantees.


Use only Legrand brand accessories.

Technical data

Shaver Socket

Cat.Nos 6 792 58

Characteristics



0 °C/+45 °C	-10 °C/+70 °C	50 mm	230 V~ 50/60 Hz	1~4 mm ²

Application

This product will be used in hotel, it can provide safe power for electric shavers. The standby power is 0W, no plug in no output power (please take care, this output to be used for electric shavers only.)

Technical partmeter

Input: 230V ~ 50/60 Hz

Output: 230V~50/60 Hz or 115V ~ 50/60 Hz


Operation

Slide switch configuration


1. Switch set to 115 V~, output is 115 V AC.
2. Switch set to 230 V~, output is 230 V AC.

Caution


1. Do not use for other application, except shaver.
2. Before plug in the shaver socket, please confirm the voltage of your product, set the right voltage 115V or 230V.



Wiring



Fixing




Safety instructions

This product should be installed preferably by a qualified electrician. Incorrect installation and use can entail risk of electric shock or fire. Before carrying out the installation, read the instructions and take account of the product's specific mounting location. Do not open up the device. All Legrand products must be exclusively opened and repaired by personnel trained and approved by LEGRAND. Any unauthorised opening or repair completely cancels all liabilities and the rights to replacement and guarantees. Only use genuine accessories.

Technical data

DND & CMR Internal and External Unit

Cat.Nos 6 792 57 / 6 794 55
6 792 56 / 6 794 54




Characteristics

voltage			Audible signal 6 792 50 - 6 794 50
230 V~ 50Hz	2 x 2.5 mm ²	- 5° C + 40° C	230 V~ 70 - 90 dB

Description

Call indicator
6 792 56 / 6 794 54



Call control
6 792 57 / 6 794 55




Option


Buzzer




Wiring



Assembly Internal Unit



External Unit




DND & CMR Internal and External Unit (contd.)

NOTES


Operation

Bedroom

1- Instruction : «Do not disturb»




2- Instruction : «PLEASE CLEAN»



3- No call




Corridor




Note

If both buttons are pressed simultaneously, priority is given to the «don't disturb» call

Bedroom



Corridor



NOTES

.....

.....

.....

.....

.....

.....

.....

.....

.....

.....

.....

.....

.....

.....

.....

.....

.....

.....

.....

.....

.....

.....

NOTES

.....

.....

.....

.....

.....

.....

.....

.....

.....

.....

.....

.....

.....

.....

.....

.....


.....

.....

.....

.....

.....



Head offices

- 61 & 62, 6th Floor,
Kalpataru Square, Kondivita Road,
Off Andheri-Kurla Road, Andheri (E),
MUMBAI – 400 059.
Tel : (022) 3041 6200
Fax : (022) 3041 6201
Website : www.legrand.co.in

Regional sales offices

- A-25, Mohan Co-operative
Industrial Estate, Mathura Road,
NEW DELHI - 110 044.
Tel : (011) 3990 2200, 2699 0046,
(011) 2699 0028 / 29 / 30 / 31
Fax : (011) 2699 0047
- Bhakta Towers, 2nd & 3rd Floor,
Plot No. KB 22, Sector-III, Saltlake,
KOLKATA – 700 098.
Tel : (033) 4021 3535 / 36
Fax : (033) 4021 3537
- C/203, Corporate Avenue, Atul Projects,
Near Mirador Hotel, Chakala,
Andheri Ghatkopar Link Road,
Andheri – East, **MUMBAI** – 400 099.
Tel : (022) 3385 6200 / 62301000 **INNOVAL**

- Ferozes Manor,
Situated at 58 Hospital Road,
Shivaji Nagar,
BANGALORE– 560 001.
Tel : (080) 6822 0000 **INNOVAL**
- 205-208, 2nd Floor, Block - II,
White House, Kundan Bagh,
Begumpet,
HYDERABAD – 500 016.
Tel : (040) 2341 4398 / 67, 4567 1717
Fax : (040) 6636 6974

Branch offices

- Unit 203, 2nd Floor, Tower- B,
Bestech Business Tower, Sector 66,
Mohali, **CHANDIGARH** -160066.
Telefax : (0141) 2208665, 666 **INNOVAL**
- 507-510, 5th Floor, Soni Paris Point,
Jai Singh Highway, Banipark,
JAIPUR - 302 016.
Tel / Fax : (0141) 220 8665 / 666
- 209-A, 2nd Floor, Cyber Heights,
Opp. Indira Gandhi Pratishthan,
Vibhuti Khand, Gomti Nagar
LUCKNOW- 226 010.
Tel : (522) 319 2031 / 32 / 33 **INNOVAL**
- 202 & 203, 2nd Floor, Sunrise,
Forum 100, Burdwan Compound, Lalpur,
RANCHI - 834 001.
- A 101-102, Mondeal Heights,
Besides Novotel Hotel, Sarkhej
Gandhinagar Highway [S G Highway],
AHMEDABAD – 380 015.
Tel : (079) 6134 0555 **INNOVAL**
- 402, Swastik Chambers,
Near Ashwamegh Marriage Hall,
Behind HP Petrol Pump,
Off Karve Road, Erandwane,
PUNE – 411 004.
Tel : (020) 6729 5601 / 602
Fax : (020) 6729 5604

- Plot No.95, II Floor, Shreyash Heights,
VIP Road, Ramdaspeth,
NAGPUR – 440 010.
Tel : (0712) 662 7857 / 858
Fax : (0712) 662 7859
- 10 B, (10th Floor), Prestige Center Court
Office Block Vijaya Forum Mall, #183,
N.S.K. Salai, Vadapalani
CHENNAI – 600 026.
Tel : (044) 6612 2800 / 2362 3125 / 35 / 45
Fax : (044) 2362 3165 **INNOVAL**
- J. B. Manjooran Estate,
Door No 50/1107A9, 3rd Floor,
Bye Pass Junction, Edappally,
COCHIN – 682 024.
Tel : (0484) 280 1921 / 2921, 658 0921 **INNOVAL**
- B-5, 1st Floor, Thirumalai Towers,
723, Avanashi Road,
COIMBATORE – 641 018.
Tel : (0422) 222 3634 / 668 3200 **INNOVAL**
- 204-205, Megapolis Square,
579, M G Road,
INDORE – 452 001.
Tel : (0731) 4999 891 / 892
- MF-2, Datta's Lords House,
Jammi Chettu Street, Mogalrajapuram,
VIJAYAWADA – 520 010.
Tel : (0866) 248 2393/6393/5393
- Plot No. 359, Saheed Nagar,
2nd Floor,
BHUBANESWAR – 751 007.
Tel : (0674) 254 0623
- Unit - 1 & 2, Vijay Park,
Main Chakrata Road,
DEHRADUN- 248 001.
Uttarakhand.
Tel : (0135) 661 6100 **INNOVAL**
- House No. 97, Ground Floor,
Rajgarh Main Road,
Opp. City Heart Nursing Home,
GUWAHATI – 781 007.
Tel : (0361) 245 8498

Area offices

- Cabin No. 9, Second Floor,
Madhok Trade Centre,
Madhok Complex, Ferozpur Road,
LUDHIANA – 141 001.
Tel : (0161) 277 0301 / 2 / 3 / 4
- 94, Udhm Singh Sarani,
Ground Floor, Ashrampara,
SILIGURI – 734 001.
Tel : (0353) 264 1067
- A-207, Universal Business
Center, Near Madhuvan circle,
L.P. Savani Road, Adajan,
SURAT - 395 009. **INNOVAL**
- Aparna Towers, 1st Floor, 2/3,
Bypass Road,
MADURAI – 625 010.
Telefax : (0452) 230 8414
- 43-9-205, Near srikanya theatre
3rd floor, Plot No 10, Subbalaskhmi
Nagar, Allipuram Ward,
Dondaparthy Area,
Vishakapathanam - 530 016.
Tel : (0891) 273 5652 / 9363 **INNOVAL**

Technical assistance from Legrand

Telephonic technical assistance for selection of products, technical information, guidance, wiring diagrams and estimation is now made available to you at each Regional Office. Contact the Technical Officer of Legrand at the following telephone numbers

New Delhi : Tel.: (011) 2699 0028, 3990 2200
Kolkata : Tel.: (033) 4021 3535 / 36
Mumbai : Tel.: (022) 3385 6200
Bangalore : Tel.: (080) 6822 0000
Hyderabad : Tel.: (040) 2341 4398 / 67, 4567 1717

For other places, contact the nearest Regional / Branch / Area offices

customer.care@legrand.co.in