


Armoires Altis™ monoblocs métal

caractéristiques techniques

Dimensions (mm)





(*) D, E (passage utile)

Dim. armoires Haut. x Larg. x Prof. (mm)	A	B	C ^(*)	D	E	G	H	I	J	L	M	N	O	P	Q
1600 x 600 x 400	1600	599	436	1507	509	460	1460	1475	475	385	255	350	550	278	478
1600 x 800 x 400	1600	799	436	1507	709	660	1460	1475	675	585	255	350	750	278	678
1600 x 1000 x 400	1600	999	436	1507	909	860	1460	1475	875	785	255	350	950	278	878
1600 x 1000 x 400	1600	999	436	1507	909	360 x 2	1460	1475	375 x 2	785	255	350	950	278	878
1600 x 1200 x 400	1600	1199	436	1507	1109	460 x 2	1460	1475	475 x 2	385 x 2	255	350	1150	278	1078
1800 x 600 x 400	1800	599	436	1707	509	460	1660	1675	475	385	255	350	550	278	478
1800 x 800 x 400	1800	799	436	1707	709	660	1660	1675	675	585	255	350	750	278	678
1800 x 1000 x 400	1800	999	436	1707	909	860	1660	1675	875	785	255	350	950	278	878
1800 x 1000 x 400	1800	999	436	1707	909	360 x 2	1660	1675	375 x 2	785	255	350	950	278	878
1800 x 1200 x 400	1800	1199	436	1707	1109	460 x 2	1660	1675	475 x 2	385 x 2	255	350	1150	278	1078
1800 x 1600 x 400	1800	1599	436	1707	1509	660 x 2	1660	1675	675 x 2	585 x 2	255	350	1550	278	1478
2000 x 600 x 400	2000	599	436	1907	509	460	1860	1875	475	385	255	350	550	278	478
2000 x 800 x 400	2000	799	436	1907	709	660	1860	1875	675	585	255	350	750	278	678
2000 x 1000 x 400	2000	999	436	1907	909	860	1860	1875	875	785	255	350	950	278	878
2000 x 1000 x 400	2000	999	436	1907	909	360 x 2	1860	1875	375 x 2	785	255	350	950	278	878
2000 x 1200 x 400	2000	1199	436	1907	1109	460 x 2	1860	1875	475 x 2	385 x 2	255	350	1150	278	1078
2000 x 1600 x 400	2000	1599	436	1907	1509	660 x 2	1860	1875	675 x 2	585 x 2	255	350	1550	278	1478
1800 x 600 x 500	1800	599	536	1707	509	460	1660	1675	475	385	355	450	550	378	478
1800 x 800 x 500	1800	799	536	1707	709	660	1660	1675	675	585	355	450	750	378	678
1800 x 1000 x 500	1800	999	536	1707	909	360 x 2	1660	1675	375 x 2	785	355	450	950	378	878
1800 x 1200 x 500	1800	1199	536	1707	1109	460 x 2	1660	1675	475 x 2	385 x 2	355	450	1150	378	1078
1800 x 1600 x 500	1800	1599	536	1707	1509	660 x 2	1660	1675	675 x 2	585 x 2	355	450	1550	378	1478
2000 x 800 x 500	2000	799	536	1907	709	660	1860	1875	675	585	355	450	750	378	678
2000 x 1000 x 500	2000	999	536	1907	909	360 x 2	1860	1875	375 x 2	785	355	450	950	378	878
2000 x 1200 x 500	2000	1199	536	1907	1109	460 x 2	1860	1875	475 x 2	385 x 2	355	450	1150	378	1078
2000 x 1600 x 500	2000	1599	536	1907	1509	660 x 2	1860	1875	675 x 2	585 x 2	355	450	1550	378	1478
1800 x 800 x 600	1800	799	636	1707	709	660	1660	1675	675	585	455	550	750	478	678
2000 x 800 x 600	2000	799	636	1907	709	660	1860	1875	675	585	455	550	750	478	678
2000 x 1200 x 600	2000	1199	636	1907	1109	460 x 2	1860	1875	475 x 2	385 x 2	455	550	1150	478	1078


1 : Dimensions hors-tout

Réglage des équipements en profondeur

Avec rail hauteur 15 mm



Positionnement des plaques pleines largeur totale



Profondeur armoire (mm)	Mini	Maxi
400	260	360
500	260	460
600	260	560