

- **1500 Capvis™**
 - **Wire connectors**
- 6 340 52**



- **AWG10**

Wire combinations

| Wire | Nb | 10 | 12 | 14 |
|------|----|----|-----|-----|
| 10 | 1 | 1 | 1-2 | 1 |
| 12 | 1 | | 1-3 | 1-5 |
| | 2 | | | 1-3 |
| 14 | 1 | | | 1-5 |

- **6 mm²**

| Capacité Capacity (mm ²) | maxi | mini |
|--|------|------|
| 2,5 ² | 5 | 2 |
| 4 ² | 3 | 2 |
| 6 ² | 2 | 2 |

EX.- I.E.: 1#12w with 1 to 5#14w

UL 94 V-2

Copper conductors only

Temperature rating: 105°C (220°F)

Building wire: 600 Vmax., signs and fixtures: 1000 Vmax.



- **Solid**
- **Rigide**

- **Stranded**
- **Souple**

- 7 strands or less
- 7 brins ou moins

- More than 7 strands
- Plus de 7 brins

