


sarlam



KALANK

NT 37 016/02

T 1 (Ø 198 mm)




T 2 (Ø 270 mm)




T1 Max.




10 W




1 W 16 Leds




T2 Max.




E27 - 60 W





T2 Max.











18W



2 x 9W




3




T 1 - T 2



Cl. I




T 2



L
N



L1
N



4

