




1. USE

Connecting device for light features.
Can be mounted on a BESA box.

2. RANGE

Ceiling Rose	Cat. No
Cover and base	0 601 95

3. DIMENSIONS (mm)



Ø A	B	C
88	30	21

4. CONNECTION

Type of terminals: with screws
Terminals capacities: 8 x 0.75 mm², 5 x 1.5 mm², 4 x 2.5 mm², 3 x 4 mm²
Stripping length: 7 mm
Tightening torque: 0.6 N
Rigid or flexible cables admissible

5. TECHNICAL CHARACTERISTICS

■ 5.1 Mechanical characteristics

Protection against mechanical impact: IK 04
Protection against solid bodies and liquids: IP 20

■ 5.2 Material characteristics

- Cover material: Urea
- Base: PC
- Terminal cover material: PC
- L/N/E terminals: Brass
- Screws: Mild steel, plated

Self extinguishing:
850°C/30 s for insulating components holding live parts in place.
650°C/30 s for other insulating components.

■ 5.3 Electrical characteristics

Voltage: 250 V~
Current: 6 A

■ 5.4 Climate characteristics

Storage temperature: -5°C to +60°C
Usage temperature: -5°C to +40°C

6. CLEANING

Surface cleaning with a cloth.
Do not use: acetone, tar remover, trichlorethylene.

Caution: A preliminary test should be carried out if specific cleaning products are to be used.

7. STANDARDS AND APPROVALS

BS 67