



Mosaic™ Cover plates

Cat. No(s): 2 778 02L/04L/06L/14L/16L/22L



2 778 02L



2 778 04L


1. USE

Plates for covering mechanisms with 2 to 3 x 2 modules.

2. RANGE

Description	White
2 modules	2 778 02L
4 modules - Horizontal	2 778 14L
6 modules - Horizontal	2 778 16L
2 x 2 modules - Horizontal	2 778 04L
2 x 2 modules - Vertical	2 778 22L
3 x 2 modules - Horizontal	2 778 06L

3. DIMENSIONS (mm)



Cat. Nos	A	B	C	D	E
2 778 02L	82	82	8.5	45.5	45.5
2 778 14L	82	153	8.5	91	45.5
2 778 16L	82	224	8.5	136	45.5
2 778 04L	82	153	8.5	45.5	45.5
2 778 06L	82	224	8.5	45.5	45.5
2 778 22L	153	82	8.5	45.5	45.5

4. TECHNICAL CHARACTERISTICS

■ 4.1 Mechanical characteristics

Impact test: IK 04

■ 4.2 Material characteristics

Halogen free

UV resistant

Material of plates: ABS White (RAL 9003) polyglass appearance

Material of subplates: PC

Self-extinguishing: 650°C/30 s

■ 4.3 Climatic characteristics

Storage temperature: - 10°C to + 70°C

Use temperature: - 5°C to + 35°C

5. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Caution: Always test before using other special cleaning products

6. SPECIAL USE

Mosaic plates must not be painted.