


## Arteor™ 3.5 mm female Jack socket

Cat. No(s): 5 720 91 - 5 725 55/59/91



### 1. USE

Allows connection of a stereo audio transmission device (iPod, notebook PC) or listening device (speaker, headsets...).

Clip fixing.

For installation in a box 40 min. depth.


### 2. RANGE

Preterminated socket - 1 module

Equipped with cord length 15 cm and 2 female connectors

White	Magnesium	Soft Alu	Champagne
5 720 91	5 725 91	5 725 55	5 725 59

### 3. DIMENSIONS (mm)



A	B	C
45	22.5	19

### 4. CONNECTION

Device to be connected.

### 5. TECHNICAL CHARACTERISTICS

#### ■ 5.1 Mechanical characteristics

Impact tests: IK 04

Protection against solid bodies and liquids: IP 40

#### ■ 5.2 Material characteristics

Base: PC

Cover: ABS (RAL 9003)


Self-extinguishing: 650°C/30 s

#### ■ 5.3 Electrical characteristics

These values are indicated for an installation set up in accordance with best practice and connected in compliance with existing standards.

Any additional accessories and cords should comply with these same criteria.

3.5 mm female audio Jack	Cable max. length	Cord max. length	Full link max. length	Min. box depth
Preterminated	5 m	2 m	9 m	40 mm



#### ■ 5.4 Climate characteristics

Storage temperature: - 10°C to + 70°C

Usage temperature: - 5°C to + 50°C

### 6. CLEANING

Surface cleaning with a cloth.

Do not use: acetone, tar remover, trichloroethylene.

Resistant to the following agents:

Hexane, Methylated spirits, Soapy water, Diluted ammonia, Pure bleach diluted to 10%, Window-cleaning products, Pre-impregnated wipes.

**Caution:** Always test before using other special cleaning products.