

Mosaic™ Programme surface-mounting boxes and adaptors



0 802 80



0 802 85



6 806 33



0 791 54



Plexo backboxes

p. 597



Selection chart for boxes, supports and plates p. 882-883

Pack	Cat.Nos	Surface-mounting boxes
5	0 802 80	For 2 modules (support Cat.No 0 802 51) Equipped with a 20 x 12.5 mm removable entry
5	0 802 81	Depth 30 mm Depth 40 mm
2	0 802 89	For 3 modules (support Cat.No 0 802 59) Equipped with a 20 x 12.5 mm removable entry Depth 40 mm
5	0 802 85	For 4, 5 or 2 x 2 horizontal modules (support Cat.No 0 802 52) Equipped with a 32 x 12.5 mm removable entry Depth 40 mm
5	0 802 86	For 6, 8 or 3 x 2 horizontal modules (support Cat.No 0 802 53) Equipped with a 32 x 12.5 mm removable entry Depth 40 mm
2	0 802 84	For 10 or 4 x 2 horizontal modules (support Cat.No 0 802 54) Equipped with a 40 x 20 mm removable entry Depth 40 mm
5	0 802 82	For 5 or 2 x 2 vertical modules (support Cat.No 0 802 52) Equipped with a 20 x 12.5 mm removable entry Depth 40 mm
5	0 802 83	For 3 x 2 vertical modules (support Cat.No 0 802 53) Equipped with a 20 x 12.5 mm removable entry Depth 40 mm
1	0 802 74	For 2 x 5, 2 x 2 x 2 modules (support Cat.No 0 802 64) or lighting environment controller Equipped with a 40 x 20 mm removable entry Depth 46 mm
1	0 802 76	For 2 x 6, 2 x 8 or 2 x 3 x 2 modules (support Cat.No 0 802 66) Equipped with a 40 x 20 mm removable entry Depth 46 mm
1	0 802 78	For 2 x 10 modules (support Cat.No 0 802 68) Equipped with a 40 x 20 mm removable entry Depth 46 mm

Pack	Cat.Nos	Modular support - 2.5 modules
10	0 802 99	For fixing Mosaic mechanisms on rail Width: 46.3 mm
		Plexo 55 modular support frames IP 55 - IK 07
		For 2-module Mosaic mechanisms Can be equipped with any Mosaic function in order to obtain an IP 55 wiring accessory
10	0 695 80	Adaptor with smoked polycarbonate flap
1	0 695 79	Adaptor with smoked polycarbonate flap lockable with special tool below (not supplied)
1	0 919 45	Security tool
		For 3-module Mosaic mechanisms Weatherproof IP 55 plate frames with membrane Allow operations of switches without opening cover maintaining IP 55 rating
10	6 806 32	White
10	6 806 33	Grey
		Adaptors for mounting on Mosaic 50 mm supports For replacing Mosaic mechanisms (50 x 50 mm) without having to change the plate or the support frame Enable a Mosaic mechanism to be mounted on Mosaic (50 x 50 mm) screw mounting support frames
10	NEW 0 791 54	Adaptor for 1-module mechanism (width 22.5 x 45 mm)
10	NEW 0 791 53	Adaptor for 2-module mechanisms (width 45 x 45 mm)

Red catalogue numbers: New products