

XL³ S 4000

universal accessories and mounting plates



XL³ S 4000

solid faceplates and fixing accessories for faceplates



3 395 40



3 395 60



3 395 88



3 395 85

Pack	Cat.Nos	Universal rails
1	3 382 43	For 16-module enclosure
1	3 382 44	For 24-module enclosure
1	3 382 45	For 36-module enclosure

Solid universal plates		
For 16-module enclosures		
		Height (mm)
1	3 395 40	200
1	3 395 41	300
1	3 395 42	400
1	3 395 43	600
For 24-module enclosures		
1	3 395 44	200
1	3 395 45	300
1	3 395 46	400
1	3 395 47	600
For 36-module enclosures		
1	3 395 48	200
1	3 395 49	300
1	3 395 50	400
1	3 395 51	600

Perforated universal plates		
For 16-module enclosures		
		Height (mm)
1	3 395 60	200
1	3 395 61	300
1	3 395 62	400
1	3 395 63	600
For 24-module enclosures		
1	3 395 64	200
1	3 395 65	300
1	3 395 66	400
1	3 395 67	600
For 36-module enclosures		
1	3 395 68	200
1	3 395 69	300
1	3 395 70	400
1	3 395 71	600

Universal support for cable sleeve		
1	3 397 51	Vertical sloping support for cable sleeve

Full-height solid mounting plates		
For installation in XL ³ S 4000 enclosures		
		For enclosures
		Height (mm) Width (mm)
1	3 381 70	2000 600
1	3 381 71	2000 800
1	3 381 72	2200 600
1	3 381 73	2200 800

Intermediate plates		
1	3 381 74	For installation in XL ³ 4000 enclosures For enclosures height 2200 mm Can be cut to height 2000 mm

Pack	Cat.Nos	Full-height solid metal faceplates			
Fixed with locking clips, 1/4 turn screws or screws					
		Faceplate total height (mm)	Faceplate usable height (mm)	Faceplate total width (mm)	Faceplate usable width (mm)
1	3 378 96	2000	1799	350	343
1	3 381 50	2200	1799	350	343

Solid metal faceplates		
Fixed with locking clips, 1/4 turn screws or screws		
Height 50 mm		
		For enclosures (modules) Faceplate usable height (mm)
1	3 395 92	16 49
1	3 395 95	24 49
1	3 395 98	36 49
Height 100 mm		
1	3 395 93	16 99
1	3 395 96	24 99
1	3 395 99	36 99
Height 150 mm		
1	3 395 94	16 149
1	3 395 97	24 149
1	3 396 00	36 149
Height 200 mm		
1	3 395 80	16 199
1	3 395 84	24 199
1	3 395 88	36 199
Height 300 mm		
1	3 395 81	16 299
1	3 395 85	24 299
1	3 395 89	36 299
Height 400 mm		
1	3 395 82	16 399
1	3 395 86	24 399
1	3 395 90	36 399
Height 600 mm		
1	3 395 83	16 599
1	3 395 87	24 599
1	3 395 91	36 599

Fixing accessories for faceplates		
1	3 397 00	Set of 100 locking clips for quick fixing
1	3 397 01	Set of 100 1/4 turn screws
1	3 397 02	Set of 100 screws